

# Eaton 266837

Catalog Number: 266837

Eaton Moeller series NZM - Molded Case Circuit Breaker. Tunnel terminal, 4p, 1 switch side, size 4

General specifications



Product Name	Catalog Number
Eaton Moeller series NZM connection type	266837
	EAN
	4015082668372
Product Length/Depth	Product Height
88 mm	90 mm
Product Width	Product Weight
212 mm	3.403 kg
Compliances	Certifications
IEC	IEC 60947
RoHS conform	EN 60947

## Product specifications

### Used with

NZM4-4, N4-4

### Type

Accessory

Tunnel terminal

### Amperage Rating

1400 A

#### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

#### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

#### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

#### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

#### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

##### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

##### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

##### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

#### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be

## Resources

### Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

### Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

### Declarations of conformity

[DA-DC-03\\_NZM4](#)

### Drawings

[eaton-general-nzm-tunnel-terminal-dimensions-002.eps](#)

[eaton-circuit-breaker-terminals-nzm-tunnel-terminal-dimensions-003.eps](#)

[eaton-circuit-breaker-terminals-nzm-tunnel-terminal-3d-drawing-005.eps](#)

### Installation instructions

[eaton-circuit-breaker-nzm4-tunnel-flat-conductor-terminal-nzm4-4-xka-xkb-instruction-leaflet-il01210012z.pdf](#)

### Installation videos

[The new digital NZM Range](#)

[Introduction of the new digital circuit breaker NZM](#)

### mCAD model

[DA-CS-nzm4\\_4\\_xka](#)

[DA-CD-nzm4\\_4\\_xka](#)

### Technical data sheets

[eaton-nzm-technical-information-sheet](#)

evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Frame

NZM4

#### Suitable for

Copper cable

Four-pole

#### Number of poles

Four-pole

#### Model

Other

#### Terminal capacity (stranded cable)

50 mm<sup>2</sup> - 240 mm<sup>2</sup> (4x)

50 mm<sup>2</sup> - 240 mm<sup>2</sup> (1x)

Max. 500 AWG/kcmil (4x)

Max. 500 AWG/kcmil (1x)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)