




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **15**

Number of Rows: **3**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	5
Number of Loaded Positions	15
Number of Power Positions	15
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	15



Number of Rows	3
----------------	---

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 – 1.79 µm[50 – 70 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Size	2.95mm
Contact Mating Area Plating Material Thickness	.76 – .91 µm[30 – 36 µin]
Contact Shape & Form	Round
PCB Contact Termination Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]
Contact Layout	Matrix
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Socket
Contact Current Rating (Max)	12 A

Termination Features

Termination Post & Tail Diameter	1.57 mm[.062 in]
Termination Post & Tail Length	5.09 mm[.2 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With



Housing Features

Mating Entry Location	Top
Housing Material	Nylon
Centerline (Pitch)	6.35 mm[.25 in]

Dimensions

Row-to-Row Spacing	6.35 mm[.25 in]
Connector Width	20.32 mm[.8 in]
PCB Thickness (Recommended)	3.18 mm[.125 in]
Connector Height	13.97 mm[.55 in]
Connector Length	33.02 mm[1.3 in]
Profile Height from PCB	14.73 mm[.58 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL, VDE
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	78
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC


Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Wave solder capable to 265°C
---------------------------	------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 350812-1 STR/REL CLAMP UMNL	 TE Part # 926647-8 UMNL CAP HSG. 15 POS	 TE Part # 350736-1 15P UMNL PLUG HSG	 TE Part # 794281-1 15P UMNL INTERFACE SEAL
 TE Part # 794745-1 15P UMNL CAP HSG BLACK	 TE Part # 926647-1 BOIT F MNL 15P	 TE Part # 926647-2 15P UN-MNL AUFN-GEH	 TE Part # 640718-1 15P UMNL STR/REL



TE Part # 1-350590-0
STR/REL CLAMP NATL




TE Part # 770023-1
15P UMNLI IN-LNE PLUG HSG KIT



TE Part # 1-640724-0
15P UMNL STR/REL & INSRT NATL



TE Part # 926647-3
UNIV.M-N-L.CAP HSG



TE Part # 794282-1
15P UMNL WIRE SEAL

Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Contacts(208)



Connector Hardware(12)



Power Contacts(208)



Rectangular Power Connectors(651)



Standard Circular Connectors(1)


Customers Also Bought



TE Part #4-2176341-5
CRGCQ 0805 47K 1%



TE Part #1-2232516-1
SCSi .050 REC ASS'Y 14P PB-FRE



TE Part #826629-5
AMPMODU II HEADER



TE Part #1609112-8
10CS1 M0=F7803






TE Part #640456-2
02P MTA100 HDR ASSY F/L SQ STR



TE Part #1-2176231-0
3522 24R 1% 3W




TE Part #213847-3
POWERBAND CONT ASSY,SILVER PLT



TE Part #1658608-2
25 POS HDF PLUG, MS, LEAD FREE



TE Part #2176186-1
CRGH1206 1% 120R 0.5W



TE Part #7-2176311-0
RP 1E 0.1W 6K04 0.1% 25PPM 1K RL

Documents

Product Drawings

15P UMNH HDR ASSY PC LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_350837-4_R.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_350837-4_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_350837-4_R.3d_stp.zip

English

Customer View Model

ENG_CVM_350837-4_L1.3d_igs.zip

English

Customer View Model

ENG_CVM_350837-4_L1.3d_stp.zip

English

Customer View Model

ENG_CVM_350837-4_L1.2d_dxf.zip

English

3D PDF

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY
English

Product Specifications
Application Specification
English

Agency Approvals
UL
English