

TRIO-PS67/1AC/24DC/3.75/M12-A - Power supply unit



1376306

<https://www.phoenixcontact.com/in/products/1376306>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Primary-switched power supply unit TRIO POWER, M12 circular connector, Panel mounting, input: 1-phase, output: 24 V DC / 3.75 A

Product description

The robust power supplies with IP67 degree of protection are ideally suited for decentral supply in the field. The weather-resistant cast-aluminum housing protects the devices against dust and water. This enables the power supplies to ensure high system availability even in harsh ambient conditions. The different device connections provide flexibility during mounting.

Your advantages

- Direct installation at the load in the field reduces cable lengths and saves space in the control cabinet
- The robust cast-aluminum housing ensures high system availability with resistance to extreme ambient conditions (temperature, dust, and water)
- High shock and vibration resistance, plus high electric strength
- Improved diagnostic options in the field with DC OK LED and AC OK LED
- NEC Class 2 (POUT <100 W)

Commercial data

Item number	1376306
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CMP
Product key	CMPF13
GTIN	4063151740160
Weight per piece (including packing)	933.6 g
Weight per piece (excluding packing)	690 g
Customs tariff number	85044095
Country of origin	VN

Technical data

Input data

AC operation

Supply system configuration	Star network (TN, TT, IT (PE))
Nominal input voltage range	100 V AC ... 277 V AC
Input voltage range	100 V AC ... 277 V AC -15 % ... +10 % 115 V AC ... 277 V AC ±10 % (UL)
Derating	< 100 V AC ... 85 V AC (1 %/V)
Switch-on voltage	≥ 80 V AC
Shut-down voltage	< 75 V AC
Typical national grid voltage	120 V AC 230 V AC
Voltage type of supply voltage	AC/DC
Inrush current	≤ 35 A (typical, 277 V AC) 17 A (typical, 120 V AC)
Inrush current integral (I^2t)	< 0.45 A ² s
AC frequency range	50 Hz ... 60 Hz ±10 %
Frequency range (f_N)	50 Hz ... 60 Hz ±10 %
Mains buffering time	> 25 ms (120 V AC) > 25 ms (230 V AC)
Current consumption	1 A (100 V AC) 0.4 A (277 V AC)
Protective circuit	Transient surge protection; Varistor
Power factor (cos phi)	> 0.92
Switch-on time	< 0.2 s
Input fuse	4 A (internal (device protection))
Recommended breaker for input protection	6 A ... 16 A (US/CAN: branch circuit protection ≤ 1 A) (Characteristic B, C, D, K or comparable)
Discharge current to PE	< 0.5 mA

DC operation

Nominal input voltage range	110 V DC ... 250 V DC
Input voltage range	110 V DC ... 250 V DC -20 % ... +10 % 120 V DC ... 250 V DC ±10 % (UL)
Derating	< 110 V DC ... 88 V DC (1 %/V)
Switch-on voltage	≥ 75 V DC
Shut-down voltage	< 70 V DC
Voltage type of supply voltage	AC/DC
Current consumption	0.88 A (110 V DC) 0.38 A (250 V DC)

Output data

1376306

<https://www.phoenixcontact.com/in/products/1376306>

Efficiency	typ. 93 % (120 V AC)
	typ. 94 % (230 V AC)
Nominal output voltage	24 V DC ± 2 %
Nominal output current (I_N)	3.75 A (Class 2 Output)
Derating	> 60 °C ... 70 °C (2.0 %/K)
Feedback voltage resistance	≤ 35 V DC
Protection against overvoltage at the output (OVP)	≤ 35 V DC
Control deviation	< 1 % (change in load, static 10 % ... 90 %)
	< 3 % (Dynamic load change 10 % ... 90 %, 10 Hz)
	< 0.1 % (change in input voltage ± 10 %)
Residual ripple	≤ 10 mV _{PP}
Short-circuit-proof	yes
No-load proof	yes
Output power	90 W
Peak switching voltages nominal load	< 100 mV
Maximum no-load power dissipation	< 0.25 W (120 V AC)
	< 0.28 W (230 V AC)
Power loss nominal load max.	< 7.4 W (120 V AC)
	< 6 W (230 V AC)
Rise time	typ. 100 ms (U_{OUT} (10 % ... 90 %))
Connection in parallel	yes, for increasing power and redundancy with diode
Connection in series	yes, for increased output voltage

Signal: DC OK

Continuous load current	100 mA
-------------------------	--------

Connection data

Input

Connection method	M12 circular connector
Coding	S
Type of locking	M12 screw locking
Number of positions	3

Output

Connection method	M12 circular connector
Coding	A
Type of locking	M12 screw locking
Number of positions	4

Signaling

Types of signaling	LED
Status display	2 x LED (green)

Signal output: LED status indicator

Signalization designation	AC OK
---------------------------	-------

1376306

<https://www.phoenixcontact.com/in/products/1376306>

Status display	LED
Color	green
AC OK	$AC_{In} > 0.76 \times AC_N$ ($AC_N = 100 \text{ V AC}$)

Signal output: LED status indicator

Signalization designation	DC OK
Status display	LED
Color	green
DC OK	$U_{OUT} > 0.9 \times U_N$ ($U_N = 24 \text{ V DC}$)

Electrical properties

Number of phases	1.00
Insulation voltage input/output	4 kV AC (type test)
	3 kV AC (routine test)

Product properties

Product type	Power supply
Product family	TRIO POWER
MTBF (IEC 61709, SN 29500)	> 1475000 h (25 °C)
	> 1000000 h (40 °C)
	> 500000 h (60 °C)

Insulation characteristics

Protection class	I
Pollution degree	2 (IEC 61010-1)

Dimensions

Item dimensions

Width	100 mm
Height	164 mm
Depth	53 mm

Drill hole

Diameter	4.2 mm
----------	--------

Installation dimensions

Installation distance right/left	20 mm / 20 mm
Installation distance top/bottom	50 mm / 100 mm

Mounting

Mounting type	Panel mounting
Assembly note	Alignable: 20 mm horizontally, 20 mm vertically above, 20 mm vertically below
With protective coating	no

Material specifications

Flammability rating according to UL 94 (housing / terminal blocks)	V0
Housing material	Metal
Type of housing	Aluminum (AlMg3)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 70 °C (Derating > 60 °C: 2 %/K)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Maximum altitude	≤ 4000 m (> 2000 m, Derating: 10 %/1000 m)
Climatic class	4K26 (EN 60721-3-4)
Max. permissible relative humidity (operation)	≤ 100 % (at 25 °C, non-condensing)
Permissible humidity (operation)	≤ 100 % (at 25 °C, non-condensing)
Shock	18 ms, 30g, in each space direction (according to IEC 60068-2-27)
Vibration (operation)	10 Hz ... 59.6 Hz, amplitude ±0.35 mm (in accordance with IEC 60068-2-6)
	59.6 Hz ... 150 Hz, 5g, 20 cycles

Standards and regulations

Overvoltage category

EN 61010-1	II (≤ 4000 m)
------------	---------------

Overvoltage category

EN 62477-1	III (≤ 2000 m)
------------	----------------

Electrical safety

Standard designation	Electrical safety
Standards/specifications	IEC 61010-1 (SELV)

Protective extra-low voltage

Standard designation	Protective extra-low voltage
Standards/specifications	IEC 61010-1 (SELV)
	IEC 61010-2-201 (PELV)

Low-voltage power supplies, DC output

Standard designation	Low-voltage power supplies, DC output
Standards/specifications	EN 61204-3

Safety requirements for electrical equipment for measurement, control, and laboratory use

Standard designation	Safety requirements for electrical equipment for measurement, control, and laboratory use
Standards/specifications	IEC 61010-1

Limit values for harmonic currents

Standard designation	Limit values for harmonic currents
----------------------	------------------------------------

1376306

<https://www.phoenixcontact.com/in/products/1376306>

Standards/specifications	EN 61000-3-2
Degrees of protection provided by enclosures (IP code)	
Standard designation	Degrees of protection provided by enclosures (IP code)
Standards/specifications	EN/IEC 60529
Mains variation/undervoltage	
Standard designation	Mains variation/undervoltage
Standards/specifications	SEMI F47 - 0706

Approvals

UL

Identification	NEC Class 2 according to UL 1310
----------------	----------------------------------

UL

Identification	UL/C-UL Listed UL 61010-1
----------------	---------------------------

UL

Identification	UL/C-UL Listed UL 61010-2-201
----------------	-------------------------------

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EC
Interference emission	Interference emission in accordance with EN 61000-6-3 (residential and commercial) and EN 61000-6-4 (industrial)
Noise immunity	Immunity in accordance with EN 61000-6-1 (residential), EN 61000-6-2 (industrial)

Conducted noise emission

Standards/regulations (Higher requirements in practice (covered))	EN 55016
	EN 61000-6-3 (Class B)
Noise emission	EN 55011 (EN 55022)
Noise emission ()	EN 55016
	EN 61000-6-3 (Class B)

Harmonic currents

Standards/regulations	EN 61000-3-2
	EN 61000-3-2 (Class A)

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electrostatic discharge

Contact discharge	6 kV (Test Level 3)
Comments	Criterion A

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

1376306

<https://www.phoenixcontact.com/in/products/1376306>

Electromagnetic HF field

Frequency range	80 MHz ... 1 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	1 GHz ... 2 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	2 GHz ... 6 GHz
Test field strength	10 V/m (Test Level 3)
Comments	Criterion A

Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

Fast transients (burst)

Input	4 kV (Test Level 3 - asymmetrical)
Output	2 kV (Test Level 3 - asymmetrical)
Comments	Criterion A

Surge voltage load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Surge voltage load (surge)

Input	1 kV (Test Level 1 - symmetrical)
	2 kV (Test Level 1 - asymmetrical)
Output	0.5 kV (Test Level 1 - symmetrical)
	0.5 kV (Test Level 1 - asymmetrical)
Comments	Criterion B

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Conducted interference

Input/Output	asymmetrical
Frequency range	0.15 MHz ... 80 MHz
Comments	Criterion A
Voltage	10 V (Test Level 3)

Voltage dips

Standards/regulations	EN 61000-4-11
Voltage	230 V AC
Frequency	50 Hz
Voltage dip	70 %
Number of periods	25 periods
Comments	Criterion A
Voltage dip	40 %
Number of periods	10 periods
Comments	Criterion B
Voltage dip	0 %

1376306

<https://www.phoenixcontact.com/in/products/1376306>

Number of periods	1 period
Comments	Criterion A

Emitted interference


Standards/regulations	EN 61000-6-3
Radio interference voltage in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential
Emitted radio interference in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential

Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.
Criterion C	Temporary adverse effects on the operating behavior, which the device corrects automatically or which can be restored by actuating the operating elements.


Drawings

Block diagram




Block diagram

Diagram




Power factor

Diagram



Output current/installation altitude

Diagram



Input current/output current


TRIO-PS67/1AC/24DC/3.75/M12-A - Power supply unit




1376306

<https://www.phoenixcontact.com/in/products/1376306>

Dimensional drawing



Device dimensions (dimensions in mm)



Efficiency

TRIO-PS67/1AC/24DC/3.75/M12-A - Power supply unit



1376306

<https://www.phoenixcontact.com/in/products/1376306>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1376306>



cULus Listed

Approval ID: FILE E 123528



cULus Listed

Approval ID: FILE E 123528

TRIO-PS67/1AC/24DC/3.75/M12-A - Power supply unit



1376306

<https://www.phoenixcontact.com/in/products/1376306>

Classifications

ECLASS

ECLASS-11.0	27040701
ECLASS-12.0	27040701
ECLASS-13.0	27040701

ETIM

ETIM 9.0	EC002540
----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	716b963e-f3ae-47f6-9cc0-c791cf6ad800

TRIO-PS67/1AC/24DC/3.75/M12-A - Power supply unit



1376306

<https://www.phoenixcontact.com/in/products/1376306>

Accessories

SAC-3P- 1,0-PVC/M12FSS PE - Power cable

1411644

<https://www.phoenixcontact.com/in/products/1411644>



Power cable, 3-position, PVC, black, free cable end, on Socket straight M12, coding: S, cable length: 1 m, For alternating current up to 16 A/690 V

SACC-M12FSS-2PEPL-CM SH - Power connector

1080227

<https://www.phoenixcontact.com/in/products/1080227>



Power connector, Power, 3-position, shielded, Socket straight M12, coding: S, Push-lock spring connection, knurl material: Brass, nickel-plated, external cable diameter 6 mm ... 11 mm

TRIO-PS67/1AC/24DC/3.75/M12-A - Power supply unit



1376306

<https://www.phoenixcontact.com/in/products/1376306>

SACC-M12MS-4PL M - Connector

1424657

<https://www.phoenixcontact.com/in/products/1424657>



Connector, Universal, 4-position, unshielded, Plug straight M12, coding: A, Push-lock spring connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4 mm ... 8 mm

SACC-M12MS-4PL SH - Connector

1424666

<https://www.phoenixcontact.com/in/products/1424666>



Connector, Universal, 4-position, shielded, Plug straight M12, coding: A, Push-lock spring connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4 mm ... 8 mm

TRIO-PS67/1AC/24DC/3.75/M12-A - Power supply unit



1376306

<https://www.phoenixcontact.com/in/products/1376306>

SAC-4P-M12MS/ 1,5-PUR - Sensor/actuator cable

1668043

<https://www.phoenixcontact.com/in/products/1668043>



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: A, on free cable end, cable length: 1.5 m

SAC-4P-M12MS/ 5,0-PUR - Sensor/actuator cable

1668069

<https://www.phoenixcontact.com/in/products/1668069>



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: A, on free cable end, cable length: 5 m

TRIO-PS67/1AC/24DC/3.75/M12-A - Power supply unit



1376306

<https://www.phoenixcontact.com/in/products/1376306>

SAC-4P-M12MS/10,0-PUR - Sensor/actuator cable

1682993

<https://www.phoenixcontact.com/in/products/1682993>



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: A, on free cable end, cable length: 10 m

STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module

1283937

<https://www.phoenixcontact.com/in/products/1283937>



Redundancy module STEP DIODE, DIN rail mounting, 5 V DC ... 24 V DC, 1x 10 A, 2x 5 A

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in