

SPAU
Pressure sensor

FESTO
Festo SE & Co. KG
Rüter Straße 82
73734 Esslingen
Germany
+49 711 347-0
www.festo.com
8111089
2019-04b
[8111091]
CE
8111089

Instructions | Operating

Translation of the original instructions

1 About this document
The operating instructions describe the entire function range. The function range is limited, depending on the product variant. You can find detailed specifications for the product, the device description file (IODD) with a description of the IO-Link® parameters and the declaration of conformity -> www.festo.com.

1.1 Applicable documents

All available documents for the product -> www.festo.com/pk.

2 Safety

2.1 General safety instructions

- The product may only be used in its original status without unauthorised modifications.
- Only use the product if it is in perfect technical condition.
- Take into consideration the ambient conditions at the location of use.
- Operate the product only with compressed air of the specified air quality class -> 13 Technical data
- Observe the specifications on the product labelling.
- Work on the product should only be conducted by qualified personnel.

2.2 Intended use

The pressure sensor SPAU is intended for monitoring pressure of compressed air and inert gases in the piping.

2.3 Area of application and approval

In combination with the UL inspection mark on the product, the information in this section must also be observed in order to comply with the certification conditions of Underwriters Laboratories Inc. (UL) for USA and Canada.

Table with 2 columns: UL approval information, Details. Includes product category code (QUYX, QUXX7), file number (E322346), considered standards (UL 61010-1, CAN/CSA C22.2 No. 61010-1), and UL mark (UL US LISTED).

Tab. 1
Only for connection to a NEC/CEC Class 2 supply.
Raccorder Uniquement a un circuit de NEC/CEC Classe 2.

WARNING!
The unit shall be supplied by a power source which fulfils the requirements on a limited-energy circuit in accordance to IEC/EN/UL/CSA 61010-1 or on a Limited Power Source (LPS) in accordance to IEC/EN/UL/CSA 60950-1 or IEC/EN/UL/CSA 62368-1 or a Class 2 circuit in accordance to NEC or CEC.

3 Service

- Contact the regional Festo contact if you have technical problems. -> www.festo.com.

4 Accessories

- Accessories -> www.festo.com/catalogue.

5 Product overview




Fig. 1 Display variant without front panel mounting. Representation of other variants can deviate from this.

6 Function

The sensor converts pneumatic pressure values (relative pressure) into electrical signals, which can be used for control or regulating functions. Measurements are carried out using a piezoresistive sensor element with a following electronic evaluation unit. Connection to the higher-level system is provided by 1 or 2 switching outputs, an analogue output and/or an IO-Link interface. The switching outputs can be configured for monitoring of a threshold value, a pressure range or a differential pressure. For each output, PNP or NPN and normally open (NO) or normally closed (NC) can optionally be set. Through the IO-Link® interface, process values can be read out and parameters changed and transmitted to additional devices.

6.1 Operating statuses

Table with 2 columns: Operating status, Function. Rows include RUN mode, SHOW mode, EDIT mode, and TEACH mode with their respective functions.

Tab. 2

6.2 Switching functions

6.2.1 Threshold value comparator for monitoring of a pressure threshold _I_

Table with 3 columns: Function, NO (normally open), NC (normally closed). Includes switching function details and pressure threshold graphs.

Tab. 3

6.2.2 Window comparator for monitoring of a pressure range _I_

Table with 3 columns: Function, NO (normally open), NC (normally closed). Includes switching function details and pressure range graphs.

1) SP.Lo = smaller pressure/vacuum value, SP.Hi = larger pressure/vacuum value, dependent on the Teach sequence

Tab. 4

6.2.3 Auto difference monitoring d _I_

This function permits monitoring of a pressure value for constancy. The applied pressure is constant in the range between [SP.Lo] and [SP.Hi], so the reference

pressure P_{Ref} is automatically determined. The result is a switching operation at the output. The signal change signals the start of pressure monitoring. If the pressure remains in the monitoring range [d.SP] around P_{Ref} , the pressure is stable. When the monitoring range is left (e.g. caused by a leakage in the system), the output switches back.




Fig. 2
The parameters [SP.Lo], [SP.Hi], [t.obS] and [d.SP] can be configured by the user. The greater [t.obS] is set, the more constant the pressure signal must be to establish the reference value P_{Ref} .

Function	NO (normally open)	NC (normally closed)
Switching function: 2 switching points (SP.Lo, SP.Hi) for setting the valid work range 1 switching point (d.SP) for determination of the monitoring area		
TEACH mode ¹⁾ : 2 teach points (TP1, TP2) - TP1 = SP.Lo, TP2 = SP.Hi		

1) SP.Lo = smaller pressure value, SP.Hi = larger pressure value, independent of the Teach sequence

Tab. 5

7 Installation
7.1 Mechanical and pneumatic

NOTICE!

An unfavourable mounting position can impair the function of the product.

- Mount the sensor so that no condensation from the compressed air lines can gather in the device.
- Install the sensor so that it cannot be heated above the maximum permissible operating temperature (plan for convection possibilities).

Installation

SPA-...-T

– Seal connecting thread.
Tightening torque: max. 10 Nm
(tightening torque M5 female thread: max. 2 Nm)

SPA-...-A

Screws: M3
Tightening torque: max. 0.5 Nm
Mounting bracket hole pattern → Fig.3

Installation

SPA-...-W

1. Wall mounting hole pattern → Fig.3

SPA-...-F

Front panel cut-out in mm

- Guide sensor from the front into the cut-out on the front panel.
- Attach the clamping plate and press until the fastening slide clips in.

Screws: M3
Tightening torque: max. 0.7 Nm
s < 2 mm: remove 1 washer
s < 1 mm: remove 2 washers

SPA-...-MS...

1.
2. Tightening torque: max. 1 Nm

Tab. 6

7.1.1 Hole patterns





Fig. 3 Left wall mounting, right mounting bracket

7.2 Electric

WARNING!

Risk of injury due to electric shock.

- For the electric power supply, use only PELV circuits that ensure a reliable electric disconnection from the mains network.
- Observe IEC 60204-1/EN 60204-1.



8.3.1 Switching output OutA

- Press the A pushbutton.
 - The first parameter set is displayed. [Fctn] flashes.

The following parameters can be displayed by repeatedly pressing the A pushbutton → Fig.5. At the end, the min. and max. values are displayed. This can be reset with the Edit pushbutton.

8.3.2 Switching output OutB or analogue output OutD

- Press B pushbutton.
 - The first parameter set is displayed. [Fctn] with OutB or [Out] with OutD flashes.

The following parameters are displayed by repeatedly pressing the B pushbutton → Fig.5.




Fig. 5

Legend for → Fig.5	
MIN, MAX	Parameter is displayed only for switching output OutA, without Timeout
●	Edit button
↓	A or B pushbutton

Tab. 11

8.4 Entering the security code

The security code must be entered when "Lock" is active.
Requirement: The sensor is ready for operation (RUN mode).

- Press the Edit button.
 - The EDIT mode is active. If the security code is activated, the parameter entry option is blocked: [Lock] flashes.
- Enter security code set with A or B pushbutton.
- Press the Edit button briefly.
 - [OutA] flashes. The parameter entry option is unblocked.

8.5 Configuring switching output (EDIT mode)



The process is the same for configuring the switching outputs for OutA and OutB. In the following, the process is described using the switching output OutA. Menu structure → Fig.7



Changing the switching behaviour of the switching outputs in the EDIT mode is effective immediately.

Requirement: The sensor is ready for operation (RUN mode).
Switching functions → 6 Function

- Press the Edit button briefly.
 - [Edit] appears. [OutA] flashes.
- Press the Edit button briefly.
 - [Fctn] flashes.
- With A or B pushbutton, select _I_ or _I_L_ or d_I_L_.
- Press the Edit button briefly.
 - The set value is saved.
 - The next adjustable parameter is shown.

- Set the parameter with A or B pushbutton.
- Repeat points 4 and 5 until all parameters are set → Fig.5.
- Press the Edit button.
 - Switch to the RUN mode.

8.6 Set analogue output (EDIT mode)

Requirement: The sensor is ready for operation (RUN mode).

- Press the Edit button briefly.
 - [Edit] appears. [OutA] flashes.
- Select [OutD] with the A pushbutton or B pushbutton.
 - [Edit] appears. [OutD] flashes.
- Press the Edit button briefly.
 - [Out] flashes.
- Set the parameter with A or B pushbutton.
- Press the Edit button briefly.
 - The set value is saved.
 - The next adjustable parameter is shown.
- Repeat points 4 and 5 until all parameters are set.
- Press the Edit button.
 - Switch to the RUN mode.

8.7 Change device settings (EDIT mode)

Requirement: The sensor is ready for operation (RUN mode).

- Press the Edit button briefly.
 - [Edit] appears. [OutA] flashes.
- With A or B pushbutton, select special menu [Spec].
 - [Spec] flashes.
- Press the Edit button briefly.
 - [Filt] flashes.
- Set the parameter with A or B pushbutton.
- Press the Edit button briefly.
 - The set value is saved.
 - The next adjustable parameter is shown.
- Repeat points 4 and 5 until all parameters are set.

8.8 Replicating parameters (EDIT mode)

Requirements:

- The pre-configured master sensor is ready for operation (RUN mode).
- Master sensor and device sensor have the same design regarding the parameters (same device ID).
- The master sensor is connected with the device sensor → Fig.6.
- Parameterisation of the device sensor must not be blocked via IO-Link.
- The device sensor is in an unswitched status (switching output PNP, display OutA off).




Fig. 6

- Select special menu [Spec] at the master sensor via device settings.
- Press the Edit button briefly until [MASt] appears.
- With A or B pushbutton, select [ON].
- Press the Edit button.
 - [REPL] / [RedY] appears.
- Press A or B pushbutton.
 - [REPL] / [RUN] appears briefly.
 - The parameters are transmitted to the device sensor.
 - [REPL] / [RedY] appears.
 - If an error occurs, an error message appears → 12 Fault clearance.
- Repeat point 5 if an additional parameter should be parameterised.
- Press the Edit button briefly.
 - Switch to the RUN mode.

8.9 Zero point synchronisation (zero adjust)

Requirement:

- The sensor is ready for operation (RUN mode).
- [Z.Adj][ON] is set → 8.7 Change device settings (EDIT mode).
- The measured value lies in the range 0 bar ± 3 % FS.

- Press the A pushbutton and B pushbutton simultaneously.
- Press the EDIT pushbutton also.
 - [OK] appears. The zero point synchronisation was successful.

If [FAIL] appears: the zero point synchronisation was not successful. Check requirements.



If [Z.Adj][OFF] is set for a later time, the device takes over the factory setting calibration values.

8.10 Menu structure (EDIT mode)

Some menu options or setting values are not applicable, depending on the selected switching function.




Fig. 7

Legend for → Fig.7

1)	The values refer to the respective measuring range. The display takes place in the selected unit.
2)	The maximum value depends on SP.Lo and SP.Hi.
●	Edit button
→	A or B pushbutton
Bold, cursive	Factory setting

Tab. 12

8.11 Teach switching points (TEACH mode)

i

The process for teaching the switching outputs for OutA (A pushbutton) and OutB (B pushbutton) is the same. In the following, the process is described using the switching output OutA.

i

There is no timeout in the TEACH mode. The sensor changes to the RUN mode only after the entire teach process is ended.

Requirement: The sensor is ready for operation (RUN mode).

If the security code is activated, the parameter entry option is blocked: [Lock] flashes.

- Entering the security code → 8.4 Entering the security code
- 1. Establish switching function in the EDIT mode
→ 8.5 Configuring switching output (EDIT mode)
- 2. Create pressure value 1.
- 3. Press the A pushbutton and Edit button.
→ The current pressure value will then be adopted as the first teaching point (TP1). [t-IN] flashes.
- 4. Create pressure value 2
- 5. Press the A pushbutton and Edit button.
→ The current pressure value is adopted as the second teaching point (TP2). Switch to the RUN mode.

9 Operation and use

NOTICE!

Property damage due to high temperatures.

Extreme pneumatic conditions (high cycle rate with large pressure amplitude) can heat the product above 80° C.

- Select the operating conditions (in particular the ambient temperature, pressure amplitude, cycle rate, current consumption) such that the product does not heat up above the maximum permitted operating temperature.

9.1 Restoring factory settings (restore)

i

By restoring the factory settings, the current settings are lost.

1. Switch off operating voltage.
2. Keep the A and B pushbuttons pressed down simultaneously.
3. Switch on the operating voltage.
4. Additionally, press the Edit button.
→ [Rsto PARM] appears. All parameters are reset to the factory settings
→ Fig.7

10 Maintenance and care

1. Switch off the energy sources (operating voltage, compressed air).
2. Clean sensor with non-abrasive cleaning agents.

11 Disassembly

1. Switch off the energy sources (operating voltage, compressed air).
2. Separate connections from the sensor.
3. Loosen the mountings.

12 Fault clearance

12.1 General

Fault description	Cause	Remedy
No display	No operating voltage or impermissible operating voltage	Apply permissible operating voltage.
	Electrical connections swapped	Connect the device in accordance with the circuit diagram.
	Device defective	Replace device.
Indicator or switching output does not react in accordance with the settings	Short circuit or overload at the output	Eliminate short circuit/overload.
	Incorrect switching point taught (e.g. at 0 bar)	Repeat teaching.
	Device defective	Replace device.
	Parameter incorrect	Reset to factory settings.

Tab. 13

12.2 Device variants with LCD display

Fault description	Cause	Remedy
[Er01] / [FAIL] ¹⁾	Device error	Replace device.
[Er02] / [ASIC] ¹⁾	Device error	Replace device.
[Er10] / [OVER] ²⁾	Measuring range exceeded	Comply with the measuring range.
[Er17] / [SUPL] ²⁾	Undervoltage	Apply permissible operating voltage.
[Er20] / [tEMP] ²⁾	Temperature fault	– Check operating conditions. – Replace device.
[Er21] / [SHRt] ²⁾	Short circuit at OutA	Eliminate short circuit.
[Er22] / [SHRt] ²⁾	Short circuit at OutB	Eliminate short circuit.
[Err] / [BUSY]	OutA is switched active in the device sensor.	Check device settings.
[Err] / [ID]	Device ID error, devices do not have the same design.	When replicating, use sensors with the same pressure range / type (same device ID).

Fault description	Cause	Remedy
[Err] / [COMM]	IO-Link® communication error	– Check line OutA. – Check settings of the device sensor.

- 1) Display flashes.
2) Display illuminates red.

Tab. 14

12.3 Device variants without LCD display

Fault description	Cause	Remedy
LED flashes red	Device error	Replace device.
LED illuminated red	Temperature error, under-voltage, measuring range exceeded, short circuit	Checking operating conditions.

Tab. 15

13 Technical data

SPAU-		
General		
Certification		RCM Mark, c UL us – Listed (OL)
CE marking (➔ declaration of conformity)		according to EU-EMC-RL Directive, according to EU-RoHS-RL Directive
Input signal/measuring element		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases Lubricated operation possible
Temperature of medium	[°C]	0 ... +50
Output, general		
Accuracy		
P16	[% FS]	±2 at room temperature
B2, B11, V1, P1, P2, P6, P10, P025, P05, V025, V05, P12	[% FS]	±1.5 at room temperature
B2, B11, V1, P1, P2, P6, P10	[% FS]	±3 in the entire temperature range
P025, P05, V025, V05, P12, P16	[% FS]	±4 in the entire temperature range
Repetition accuracy	[% FS]	±0.3 (short-time), with [Filt] = [OFF]
Temperature coefficient	[%FS/K]	typ. ± 0.05
Switching output		
Switch-on time	[ms]	max. 4.4 with [Filt] = [OFF]
Switch-off time	[ms]	max. 5.3 with [Filt] = [OFF]
Max. output current	[mA]	100
Capacitive load maximum DC	[nF]	100
Voltage drop	[V]	Max. 1.6
Pull-down/pull-up resistor	PNP: integrated; NPN: not integrated	
Inductive protective circuit	Available	
Analogue output		
Output characteristic curve start value ... end value		
SPAU-...-V	[V]	0 ... 10
SPAU-...-B	[V]	1 ... 5
SPAU-...-A	[mA]	4 ... 20
Rise time	[ms]	3, at [Filt] = [OFF]
Max. load resistance of current output (SPAU-...-A)	[Ω]	500
Min. load resistance of voltage output (SPAU-...-V, SPAU-...-B)	[kΩ]	10
Additional output data		
Short circuit current rating	Yes	
Overload protection	Available	
Electronic system		
Operating voltage range	[V]	20 ... 30
Idle current	[mA]	Typically 35
Ready-state delay	[ms]	Typically 160
Reverse polarity protection	All connections against each other	
Mechanical system		
Mounting position	Any, avoid condensation gathering in the sensor	
Housing material	PA reinforced	
Material of keypad	TPE-O	
Material of plug housing	Brass (nickel-plated)	
Display/operation		
Displayable units	bar, kPa, MPa, psi, mmHg, inchHg, inchH2O, kgf/cm2	
Threshold value setting range	[% FS]	0 ... 100 (recommended range 1 ... 99)

SPAU-		
Threshold value setting range, auto difference monitoring	[% FS]	0.5 ... 100
Hysteresis setting range	[% FS]	0 ... 90
Immissions/emissions		
Storage temperature	[°C]	–20 ... +80
Ambient temperature	[°C]/[°F]	0 ... +50 / 122
Degree of protection to EN 60529		
SPAU-...-T/H/W/A	IP65/IP67	
SPAU-...-F/MS4/MS6	IP65	
Protection class in accordance with DIN VDE 0106-1	III	
Resistance to shocks in accordance with EN 60068-2	30 g acceleration with 11 ms duration (half-sine)	
Vibration resistance in accordance with EN 60068-2	10 ... 60 Hz: 0.35 mm / 60 ... 150 HZ: 5g	

Tab. 16

SPAU-...		-B2	-B11	-V025	-V05	-V1	-P025	-P05
Pressure measuring range initial value	[bar] [MPa]	-1 -0.1		0 0				
Pressure measuring range end value	[bar] [MPa]	1 0.1	10 1	-0.25 -0.025	-0.5 -0.05	-1 -0.1	0.25 0.025	0.5 0.05
Overload range initial value	[bar] [MPa]	-1 -0.1						
Overload range end value	[bar] [MPa]	5 0.5	15 1.5	1 0.1	2 0.2	5 0.5	1 0.1	2 0.2

Tab. 17

SPAU-...		-P1	-P2	-P6	-P10	-P12	-P16
Pressure measuring range initial value	[bar] [MPa]	0 0					
Pressure measuring range end value	[bar] [MPa]	1 0.1	2 0.2	6 0.6	10 1	12 1.2	16 1.6
Overload range initial value	[bar] [MPa]	-1 -0.1					
Overload range end value	[bar] [MPa]	5 0.5	6 0.6	15 1.5			20 2.0

Tab. 18

IO-Link®	
Protocol version	Device V1.1
Profile	Smart Sensor profile
Function classes	Binary data channel (BDC), Process data variable (PDV), Identification, diagnostics, Teach channel
Communication mode	COM2 (38.4 kBaud)
SIO mode support	Yes
Port class	A
Process data width OUT	0 bytes
Process data width IN	2 bytes
Process data content	2 bit BDC (pressure monitoring), 14 bit PDV (pressure measurement value)
Minimum cycle time	3 ms
Data memory required	< 2 kByte
IODD, IO-Link® device description	➔ www.festo.com

Tab. 19

Electrical data and ambient conditions UL/CSA	
Input current	max. 0.24 A
Power	max. 7.2 W
Pressure differential	max. 1.6 MPa
Pollution degree	3
Humidity range	93 %
Installation site	for indoor use only
Max. installation height	2000 m
Degree of protection	The degree of protection IP65/IP67 is not UL-tested.

Tab. 20 Electrical data and ambient conditions UL/CSA