



Glass Cloth Tape

361

Technical Data

March, 2014

Product Description 3M™ Glass Cloth Tape 361 is coated with a silicone adhesive for many applications requiring high temperature resistance, high adhesion and a very strong, abrasion-resistant backing.

| Product Construction | Backing | Adhesive | Color | Standard Roll Length | Standard Widths |
|----------------------|-------------|----------|-------|----------------------|---|
| | Glass cloth | Silicone | White | 60 yds. (55 m) | 1/2, 3/4, 1, 1 1/2, 2, 3 in. (13, 19, 25, 38, 50, 75 mm) |

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

| | ASTM Test Method |
|------------------------|---|
| Adhesion to Steel: | 38 oz./in. width (42 N/100 mm) D-3330 |
| Tensile Strength: | 146 lbs./in. width (2555 N/100 mm) D-3759 |
| Elongation at Break: | 9% D-3759 |
| Backing Thickness: | 5.0 mils (0.13 mm) D-3652 |
| Total Tape Thickness: | 6.4 mils (0.16 mm) D-3652 |
| Temperature Use Range: | -65° to 450°F (-54° to 232°C) |

Features

- Can be certified to meet F.A.R. 25.853, flame resistant specification.
- Can withstand intermittent temperatures up to 550°F (288°C) or higher, depending upon the type and duration of the heat source.
- Continuous exposure to temperatures above 450°F (232°C) will gradually degrade the adhesive causing loss of tape adhesion and darken the glass cloth backing.

Application Ideas

- High temperature applications requiring high tensile strength, good holding power and abrasion resistance.
- Permanent sealing of high temperature ducts or chambers.
- As a back up strip for submerged arc welding.
- Applications requiring heat treatment followed by clean removal of the tape with little or no stain.

3M™ Glass Cloth Tape

361

Storage Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 50% R.H. in the original carton.

Shelf Life To obtain best performance, use this product within 24 months from date of manufacture.

Product Use All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



**Industrial Business
Industrial Adhesives and Tapes Division**

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (fax)
www.3M.com/iatd



*Recycled Paper
40% pre-consumer
10% post-consumer*

Printed in U.S.A.
©3M 2014 (3/14)