

DCH735X2-QW

54V XR FLEXVOLT 48mm SDS-Max Hammer Drill - 2 X 9Ah



5035048747384



Product Description :

The DEWALT® 54V brushless motor and high capacity battery delivers 13.3 Joules of impact energy which offers a maximum drilling capacity of 48mm in solid concrete. Despite its high performance the DCH735 features class leading vibration of 9.0m/s² thanks to Perform and Protect features including an Active Vibration Control handle and an anti-rotation system which detects a loss of tool control and reacts instantly by cutting power.

Product Features and Benefits :

- An anti-rotation system detects a loss of tool control, and reacts by instantly cutting the power
- Active vibration control system incorporating a floating handle delivers extremely low vibration of 9.6m/s² when drilling in concrete and 9m/s² when in chiselling mode. Reduces fatigue whilst increasing safety, comfort and productivity
- Rotation-stop for demolition applications in brick, masonry and light chasing in concrete
- Wireless Tool Control transmitter which allows the tool to be wirelessly paired with another Wireless Tool Control device, such as a dust extractor, for automatic activation and shut down
- Brushless motor for improved runtime and reduced maintenance
- Perform & Protect: low vibration at 9m/s², minimising user fatigue[fr]
- Electronic speed and impact energy control
- Ideal for drilling anchor fixing and through holes in concrete and masonry up to 48 mm in diameter. Core drilling up to 125 mm
- Service and anti-rotation system LED indicators

Technical specifications :

- Battery Capacity : 9 Ah
- Weight (Including Battery) [Metric] : 10 Kg
- Tool Holder [Imperial] : SDS-Max
- Vibration Measurement (Chiseling) : 8.8 m/s²
- Optimum Drilling Range [Metric] : 25 - 38 mm
- Vibration Measurement (Drilling) : 9 m/s²

Product Warranty :

1 Year Limited Warranty, 3 Year Limited Warranty When Registered

Included items :

- 9.0Ah XR FLEXVOLT Battery Pack With State of Charge Indicator (x2)
- Multi-Voltage Charger (x1)
- Multi-Position Side Handle (x1)
- Heavy Duty Carrying Case (x1)

