


**Part Number :** [353280360](#)

**Product Description :** 7.92mm Pitch Header,  
Vertical, Positive Lock, Shrouded, 3 Circuits, White, PA  
Polyamide (Nylon) 6/6, Glass-filled

**Series Number :** 35328

**Status :** Obsolete

**Product Category :** PCB Headers and Receptacles




## Documents & Resources

### Specifications

[PS-35156-005-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Obsolete
Category	PCB Headers and Receptacles
Series	35328
Description	7.92mm Pitch Header, Vertical, Positive Lock, Shrouded, 3 Circuits, White, PA Polyamide (Nylon) 6/6, Glass-filled
Application	Power, Wire-to-Board
Component Type	PCB Header
Product Name	N/A
UPC	822348697632

### Agency

CSA	LR19980
UL	E29179

### Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

### Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No

Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.226/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.40mm
Pitch - Mating Interface	7.92mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
3.96mm Pitch Wire-to-Board Housing, Positive Lock, Natural, 5 Circuits	<u>351560500</u>