



WRECKER 150mm x 7/11 Tpi - 5 pc

MULTI MATERIAL: HEAVY DUTY WRECKER™ BLADES

- Strong and precise: Thick 1.27 mm blade body.
- Bi-Metal construction: Excellent blade life and performance.
- Tooth geometry: Aggressive strengthened tooth tip design and uniform gullet depth allows for more material to be removed per stroke for faster cutting.
- Blade shape: Sloped - The sloped shape makes this blade ideal for plunge cutting. Most suited for cutting metal and for demolition applications (wood with nails).



Article Number	48475701
Blade length (mm)	150
Max. cutting capacity cast iron pipe (mm)	10 - 100
Max. cutting capacity metal pipe (mm)	10 - 100
Max. cutting capacity non-ferrous metals (mm)	4 - 10
Max. cutting capacity steel (mm)	4 - 10
Max. cutting capacity wood with nails (mm)	10 - 100
Pack quantity	5
Plunge cut	Yes