



## Main

Range	New Unica
Product or component type	TV socket
Device application	Media device support -
Device presentation	Mechanism
TV socket type	Individual
Colour tint	Anthracite (RAL 7021)

## Complementary

TV connector	Male IEC 9.52 mm
Path attenuation	1.5 dB TV signal
DC current flow	Yes
Number of modules	1 module
Material	Thermoplastic ABS-UV stabilised: central plate
Surface treatment	Painted
Surface finish	Matt
Marking	Without marking
Device mounting	Flush
Fixing mode	Clip-in
Depth	35.5 mm
Width	22.5 mm
Height	45 mm
Embedding depth	35.5 mm
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...35 °C
Standards	CE

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Minimum percentage of recycled plastic content	4