




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	00	P2		REVISED PER ECO-11-004587	11MAR11	RK

- 1 0.000381 [.000015] GOLD IN THE CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3 THE NOTED DIMENSIONS APPLY FROM THE BASIC DIMENSION LINE (NOT THE POST CENTERLINE) TO THE SURFACE INDICATED
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS. ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5 DIMENSIONS NOTED ARE FOR SOLDER STENCIL LAYOUT FOR USE WITH A 1.57±0.20 [.062±.008] THICK. PRINTED CIRCUIT BOARD
- 6 PARTS ARE PACKAGED IN GANG OF TUBES
- 7 0.000381 [.000015] GOLD IN THE CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN ON THE SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

SEE SHEET 2 FOR PART NUMBER TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G DOUTY 2-22-88	 TE Connectivity		
		CHK T C CLARK 2-22-88			
DIMENSIONS: mm [INCHES]		APVD T C CLARK 2-22-88	NAME		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		HEADER ASSY, AMPMODU MTE, RIGHT ANGLE, SINGLE ROW, .100 POSTS, WITH LATCH & HOLD DOWNS		
	0 PLC ± -				
	1 PLC ± -				
	2 PLC ± 0.13 [.005]				
	3 PLC ± -				
4 PLC ± -					
ANGLES ± ±		PRODUCT SPEC	SIZE		
		APPLICATION SPEC			
		FINISH	CAGE CODE		
MATERIAL HOUSING: HIGH TEMPERATURE THERMOPLASTIC, COLOR- BLACK		WEIGHT -	DRAWING NO		
POSTS: BRASS		SEE TABLE	RESTRICTED TO		
		CUSTOMER DRAWING	A2 00779 C=104361		
			SCALE 4:1		
			SHEET 1 of 2		
			REV P2		

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	OWN	APVD
			-	SEE SHEET 1	-	-	-

⚠	SUPERSEDED BY 7-104361-4
⚠	SUPERSEDED BY 7-104361-3
⚠	SUPERSEDED BY 7-104361-2
⚠	SUPERSEDED BY 7-104361-1
⚠	SUPERSEDED BY 7-104361-0
⚠	SUPERSEDED BY 6-104361-8
⚠	SUPERSEDED BY 6-104361-7
⚠	SUPERSEDED BY 6-104361-6
⚠	SUPERSEDED BY 6-104361-5
⚠	SUPERSEDED BY 6-104361-4
⚠	SUPERSEDED BY 6-104361-2
⚠	SUPERSEDED BY 6-104361-0

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 2--22--88 G DOUTY		 TE Connectivity	
		CHK 2--22--88 T C CLARK			
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME HEADER ASSY, AMPMODU MTE, RIGHT ANGLE, SINGLE ROW, .100 POSTS, WITH LATCH & HOLD DOWNS	
		APVD 2--22--88 T C CLARK			
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL		FINISH		SIZE A2	
SEE TABLE		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C=104361	
				RESTRICTED TO -	
				SCALE 4:1	
				SHEET 2 of 2	
				REV P2	