


## FEATURES

- **Annealed Copper Conductor:** Provides superior conductivity and durability.
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors and mechanical wear.
- **Wide Temperature Range:** Operates effectively from -15 °C to 70 °C, suitable for diverse environments.
- **500 V Voltage Rating:** Ensures compatibility with a wide range of electrical systems.
- **2 Core Design:** Simplifies installation in various applications.
- **10.6 mm Outside Diameter:** Allows for easy routing and installation in confined spaces.

## RS PRO 2.5 mm<sup>2</sup> Flexible Cable, 100 m Length

RS Stock No: 606-132



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial settings. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable is suitable for installations where flexibility and a robust performance are required, making it ideal for both indoor and outdoor applications.

## General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

## Mechanical Specifications

Cable CSA	2.5 mm <sup>2</sup>
Cable Length	100 m
Core Strands	50/0.25
Jacket Material	Polyvinyl Chloride
Number of Cores	2
Outside Diameter	10.6 mm

## Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

## Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

## Electrical Specifications

Voltage	500 V
---------	-------