

ANIKA EVO

T925KBI055L51-10 DOM18

EAN 4031582497946

Swivel castor with wheel brake, housing made of biosourced Polyamide, with blind hole fitting. Wheel centre made of biosourced Polyamide, tread made of biosourced Polyurethane, plain bearing (soft wheel)



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product


Technical Data

Wheel diameter	55 mm
Wheel width	11 mm
Castor width	37 mm
Centre hole	10 mm
Dome-Ø	18 mm
Swivel Interference	128 mm
Overall height	57 mm
Temperature	- 10 / + 40 °C
Standard	EN_12528
Weight	0.65 kg
Swivel Radius	64 mm
Load capacity	40 kg
Load capacity (static)	80 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

Dimensions



Structure & Mounting

