


PSR-M-CABLE100 - Cable

1104834

<https://www.phoenixcontact.com/in/products/1104834>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connection cable for TBUS extension in connection with PSR-M-TBUS1 or PSR-M-TBUS2, 100 m

Commercial data

Item number	1104834
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	DNA366
GTIN	4055626972510
Weight per piece (including packing)	10.5 kg
Weight per piece (excluding packing)	7.5 kg
Customs tariff number	85444995
Country of origin	IT

PSR-M-CABLE100 - Cable

1104834

<https://www.phoenixcontact.com/in/products/1104834>



Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type

Adapter cable

Electrical properties

Impedance

nom. 120 Ω

Dimensions

External dimensions

External diameter max.

9.00 mm

Material specifications

Outer sheath, material

PVC

Cable/line

Cable length

100 m

Cable structure

2 x 2 x 24 AWG

External cable diameter

8.70 mm

Outer sheath, material

PVC

External sheath, color

yellow

Shielding

Braided copper wires

Cable resistance

< 95 m Ω /m

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)

-30 °C ... 60 °C

PSR-M-CABLE100 - Cable

1104834

<https://www.phoenixcontact.com/in/products/1104834>



Classifications

ECLASS

ECLASS-11.0	27371392
ECLASS-13.0	27371392
ECLASS-12.0	27371392

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

PSR-M-CABLE100 - Cable



1104834
<https://www.phoenixcontact.com/in/products/1104834>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in