





www.cif.fr

Carbide tungsten drill
Diameter 1.5 mm
DU75

This document contains manufacturer's information, protected through copyright. All rights reserved. This document can not be copied, reproduced or translated without written agreement from **C.I.F**

Information contained in this document can be modified without any prior notice

CHARACTERISTICS**Carbure tungsten drill bit**

- Monopiece. Queue reinforced 3,17
- Diameter : 1.5 mm
- Minimum drilling speed 20 000 tr/min
- Most little is the diameter, higher will be the speed
- Descent speed from 1,6 to 4 m/min
- Option, drill bits with ring

UTILISATION

General use for drilling on different type of PCB support such as epoxy (typical use), EMC-1, EMC-3, etc..

cif@cif.fr