

ENGLISH

Datasheet

RS Pro Prominent Indicator Panel Mount, 22mm Mounting Hole Size, Green LED, Tab Termination, 16 mm Lamp Size RS Stock No: 212-222



Product Details

RS Pro prominent indicator with 22 mm mounting hole, features green LEDs for panel mount applications. This indicator accommodates a lamp size of 18 mm and offers faston, solder lug termination. It has a voltage rating of 24 to 36 V dc. The indicator has a wide operating temperature range of -40 to +85°C, further increasing the potential applications they may be used for. The 18 mm LED requires a 22 mm panel cut-out and is supplied with a fixing nut and spring washer. It offers a wide selection of voltage ratings, bezel finishes and bezel styles.

Features and Benefits

- 22 mm panel mounting LED indicator
- Coloured diffused epoxy lens or water clear super bright LEDs
- Prominent, recessed, chamfer and flush bezel styles
- Operating temperature range: -40 to +85°C



ENGLISH


Specifications:

Bezel Colour	Black Chrome
Dezei Guiuui	DIACK CHILOTTIE
Bezel Style	Prominent
Current Rating	40 mA
Intensity	95 mcd
Lamp Size	18 mm
Lamp Type	LED
Length	41.5 mm
Light Output Colour	Green
Mounting Hole Size	22 mm
Termination Type	Faston, Solder Lug
Type	Panel Mount
Voltage Rating	24 to 36 V dc
Temperature Rating	-40 to +85°C
Type of Illumination	Fixed Light
LED Colour	Green



TECHNICAL SPECI	FICATIONS	
Voltage	Operating Voltage	Operating Current
_	(Min to Max)	(Typical All Types)
	·	
05 (No Resistor)	3.3 to 9.9VDC	40mA max*
12VDC	10.8 to 13.2VDC	40mA
24VDC	21.6 to 26.4VDC	40mA
28VDC	25.2 to 30.8VDC	40mA
110VAC	99 to 121VAC	5mA
220VAC	207 to 253VAC	3mA

ENGLISH



Standard LED Intensity	Prominent and Recessed	Flush	Forward Voltage	
HE Red	82mcd	70mcd	5.7V	
Green	95mcd	66mcd	6.0V	
Yellow	60mcd	59mcd	5.9V	
Blue	120mcd	101mcd	9.9V	
White	1,000mcd	150mcd	3.3V	
Bi-color (Typical) (Red/Green)	80/50mcd	80/50mcd	2.0V/2.2V	
Tri-color (Typical) (Red/Green/Yellow)	80/50/50mcd	80/50/50mcd	2.0V/2.2V/2.1V	
Bi-color - The color is changed by reversing the polarity of the supply voltage.				

Tri-color - The indicator has red and green LEDs, when both connected yellow is produced.

800mcd	5.7V
980mcd	9.0V
1,250mcd	6.0V

Luminous intensity will be reduced with lower operating current.

Note: The operating voltage must not be exceeded by more that 10% as this will result in reduced life expectancy.

The company reserves the right to change specifications without notice.

* Customer to supply resistor for desired operating current.

Luminous intensity is measured at 20mA on a discrete LED unless otherwise stated.

Luminous intensities and color shades of white LEDs may vary within a batch.

LED characteristics are dependent upon environmental conditions. Therefore published data should be considered nominal.



Technical Drawings

PROMINENT BEZEL

ENGLISH

