

# ML10/13.SFD

ABB contact for United  
States of America



## General Information

|                               |  |
|-------------------------------|--|
| <b>Extended Product Type:</b> | ML10/13.SFD  |
| <b>Product ID:</b>            | 1SNA199166R2600  |
| <b>EAN:</b>                   | 3472591991666  |
| <b>Catalog Description:</b>   | ML10/13.SFD Screw Clamp Terminal Blocks - For 6.3 x 25 and 6.3 x 32 fuses - with blown fuse indicator by Neon 480V - Black |
| <b>Long Description:</b>      | ML10/13.SFD Screw Clamp Terminal Blocks Fuse   |

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Screw Clamp Terminal Blocks

## Ordering

|                                |               |
|--------------------------------|---------------|
| <b>EAN:</b>                    | 3472591991666 |
| <b>Minimum Order Quantity:</b> | 20 piece      |
| <b>Customs Tariff Number:</b>  | 85361050      |

## Dimensions

|                            |         |
|----------------------------|---------|
| <b>Product Net Width:</b>  | 13.0 mm |
| <b>Product Net Height:</b> | 85.0 mm |
| <b>Product Net Depth:</b>  | 58.0 mm |
| <b>Product Net Weight:</b> | 54.00 g |

## Container Information

|                                      |               |
|--------------------------------------|---------------|
| <b>Package Level 1 Units:</b>        | 20 piece      |
| <b>Package Level 1 Width:</b>        | 172 mm        |
| <b>Package Level 1 Height:</b>       | 71 mm         |
| <b>Package Level 1 Length:</b>       | 155 mm        |
| <b>Package Level 1 Gross Weight:</b> | 1.08000 kg    |
| <b>Package Level 1 EAN:</b>          | 3472591991666 |
| <b>Package Level 2 Units:</b>        | 200 piece     |
| <b>Package Level 2 Width:</b>        | 300 mm        |
| <b>Package Level 2 Height:</b>       | 300 mm        |
| <b>Package Level 2 Length:</b>       | 500 mm        |
| <b>Package Level 2 Gross Weight:</b> | 11.300 kg     |
| <b>Package Level 3 Units:</b>        | 4800 piece    |
| <b>Product Packing Type:</b>         | Box           |

## Environmental

|                     |   |
|---------------------|---|
| <b>RoHS Status:</b> | Following EU Directive 2002/95/EC August 18, 2005 and amendment |
|---------------------|---|

## Technical UL/CSA

|   |                                      |
|---|--------------------------------------|
| <b>Maximum Operating Voltage UL/CSA:</b>        | Main Circuit 600 V                   |
| <b>Connecting Capacity-Main Circuit UL/CSA:</b> | Screw Clamp / Rigid 1x 22 ... 10 AWG |
| <b>Connecting Capacity UL/CSA:</b>              | Screw Clamp / Rigid 22 ... 10 AWG    |

Flammability According to UL94: V0

---

### Additional Information

---

|  |  |
|--|--|
| Color:   | Black  |
| Connecting Capacity-Main Circuit:                    | Screw Clamp / Flexible 1x 0.5 ... 10 mm <sup>2</sup><br>Screw Clamp / Rigid 1x 0.5 ... 16 mm <sup>2</sup>  |
| Connection Type:                                     | Screw clamp  |
| Function:  | Fuse   |
| Gauge Type:  | A6   |
| IIT Publishing Status:                               | Level 0 - Information enabled  |
| Mounting on DIN Rail:                                | G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715<br>TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715<br>TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |
| Number of Levels:                                    | 1  |
| Pollution Degree:                                    | 3  |
| Product Main Type:                                   | ML10/13.SF   |
| Product Name:  | Terminal block   |
| Rated Cross-Section:                                 | 10 mm <sup>2</sup>   |
| Rated Current (I <sub>n</sub> ):                     | Main Circuit 10 A  |
| Rated Impulse Withstand Voltage (U <sub>imp</sub> ): | 8000 V   |
| Rated Voltage (U <sub>r</sub> ):                     | 800 V  |
| Recommended Screw Driver:                            | 5.5 mm   |
| RoHS Date:   | 20050818   |
| Spacing:   | 13 mm  |
| Sub-Function:  | For 6.3x25 and 6.3x32 Fuses  |
| Sub-Function 2:                                      | With blown fuse indicator by LED 24V   |
| Wire Stripping Length:                               | 12.0 mm  |

---

### Certificates and Declarations (Document Number)

---

|                                 |                     |
|---------------------------------|---------------------|
| CSA Certificate:                | TBD - OK in Ag.Base |
| cUL Certificate:                | TBD - OK in Ag.Base |
| Declaration of Conformity - CE: | 1SND225007C1006     |
| GOST Certificate:               | 1SND161005A1104     |
| RoHS Information:               | 1SND230023F0206     |

---

### Classifications

---

|                             |                                |
|-----------------------------|--------------------------------|
| ETIM 4.0:                   | EC000899 - Fuse terminal block |
| ETIM 5.0:                   | EC000899 - Fuse terminal block |
| Object Classification Code: | X                              |

---

