

## FEATURES

- Switched six socket power strip
- 16A Type CEE 7/4 Shucko Sockets
- 2m Cable
- Operating Temperature Range of -25°C to +70°C

## RS PRO 2m 4 Socket Type G - British Trailing Socket, 230 V ac

RS Stock No.: 374-200



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This 6 way Schuko Surge & RFI protected socket strip is an ideal solution for home, office and industrial use.

This trailing socket features a 2 metre lead fitted with a CEE7/7 Schuko Type F plug feeding six CEE7/4 Schuko Type F sockets in an aluminium case for high impact resistance and long life.

## General Specifications

<b>Type</b>	Socket Strip
<b>Colour</b>	Grey
<b>Number of Sockets</b>	6
<b>Surge Protection</b>	Yes
<b>Switchable</b>	Yes
<b>RCD Protected</b>	Yes
<b>Wired</b>	Yes
<b>Fused</b>	Yes
<b>Response Time</b>	<10ns
<b>Corded</b>	Yes
<b>Overload protection</b>	Yes
<b>Power Indicator</b>	Yes
<b>Application</b>	Mobile phone chargers, including those with a USB connectivity, Household entertainment (TVs, satellite boxes, routers etc.), Industrial machines and equipment, Office desks (Monitors, computers, phones), Any electrical device needed to be powered by the mains

## Electrical Specifications

<b>Main Plug Type</b>	CEE 7/7 German Schuko / French
<b>Socket Type</b>	Type F - German Schuko
<b>Voltage Rating</b>	250V ac
<b>Current Rating (Unwound)</b>	12.5A
<b>Frequency</b>	50/60Hz
<b>Surge Handling (8/20µs)</b>	19.5kA [6.5kA]
<b>Voltage Protection Level (Up) 8/20µs</b>	900V@3kA 8/20µs

## Mechanical Specifications

<b>Cable Length</b>	2m
---------------------	----

## Operation Environment Specifications

<b>Operating Temperature</b>	-25°C to +70°C
------------------------------	----------------

## Approvals

<b>Compliance/Certifications</b>	EN61340
<b>Standards Met</b>	RoHS Compliant



