

Servo motor EMMH-AS-138-MKA-HS-S1MB-T

Part number: 8215368

FESTO



 General operating condition

Data sheet

Feature	Value
Ambient temperature	-30 °C ... 40 °C
Note on ambient temperature	Up to 80°C with derating -2%/°C
Max. installation height	3000 m
Note on max. installation height	As of 1,000 m: only with derating of -1.0% per 100 m
Storage temperature	-20 °C ... 70 °C
Relative air humidity	0 - 100%
Conforms to standard	IEC 60034
Temperature class as per EN 60034-1	F
Max. winding temperature	155 °C
Rating class as per EN 60034-1	S1
Temperature monitoring	Digital motor temperature transmission via EnDat® 2.2
Motor type to EN 60034-7	IM B14 IM V18
Mounting position	Any
Degree of protection	IP69K
Concentricity, coaxiality, axial runout to DIN SPEC 42955	N
Balance quality	G 2.5
Detent torque	<1.0% of peak torque
Bearing lifetime under nominal conditions	20000 h
Interface code, motor out	138C
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connector system	M17x0.75
Electrical connection 1, number of connections/cores	15
Electrical connection 1, connection pattern	00997714
Pollution degree	2
Note on materials	RoHS compliant
Corrosion resistance class CRC	4 - Very high corrosion stress (except laser marking)
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	Approved for direct contact with food
Vibration resistance	As per EN 60068-2-6
Shock resistance	As per EN 60068-2-29 15 g/11 ms to EN 60068-2-27
Approval	RCM
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive

Feature	Value
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
Nominal operating voltage DC	680 V
Type of winding switch	Star inside
Number of pole pairs	5
Standstill torque	11 Nm
Nominal torque	6.2 Nm
Peak torque	33.3 Nm
Nominal rotary speed	2000 rpm
Max. rotational speed	4590 rpm
Max. mechanical speed	5000 rpm
Angular acceleration	$\leq 100000 \text{ rad/s}^2$
Nominal power rating of motor	1300 W
Continuous stall current	7.4 A
Nominal motor current	4.3 A
Peak current	23.1 A
Motor constant	1.47 Nm/A
Standstill torque constant	1.51 Nm/A
Voltage constant, phase-to-phase	97.6 mV/min
Phase-phase winding resistance	0.89 Ohm
Phase-phase winding inductance	8.8 mH
Winding longitudinal inductivity Ld (phase)	3.9 mH
Winding cross inductivity Lq (phase)	4.4 mH
Electric time constant	9.8 ms
Thermal time constant	100 min
Thermal resistance	0.68 K/W
Measuring flange	300 x 300 x 30 mm, steel
Mass moment of inertia of rotor	9.78 kgcm ²
Total mass moment of inertia of output	12.1 kgcm ²
Product weight	14400 g
Permissible axial shaft load	227 N
Permissible radial shaft load	1135 N
Rotor position sensor	Absolute encoder, multi-turn
rotor position sensor, manufacturer designation	EQI 1331
rotor position sensor, absolute detectable revolutions	4096
Rotor position encoder interface	EnDat 22
Rotor position sensor, encoder measuring principle	Inductive
rotor position sensor, DC operating voltage	5 V
rotor position sensor, DC operating voltage range	3.6 V ... 14 V
rotor position sensor, position values per revolution	524288
Rotor position transducer resolution	19 bit
rotor position sensor, system accuracy of angle measurement	-65 arcsec ... 65 arcsec
Brake holding torque	20 Nm
Operating voltage DC for brake	24 V
Brake current consumption	0.68 A
Power consumption, brake	16.4 W
Brake coil resistance	35.3 Ohm
Brake coil inductivity	3200 mH
Brake separation time	90 ms
Brake closing time	81 ms
DC brake response delay	10 ms
Max. brake no-load speed	10000 rpm
Max. friction per braking process	1980 J

Feature	Value
Number of emergency stops per hour	1
Total brake friction	1980 kJ
Mass moment of inertia of brake	2.32 kgcm ²
Switching cycles holding brake	10 million idle actuations (without friction work!)
Mean time to failure (MTTF), subcomponent	190 years, rotor position encoder