



**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS002430\_3\_20191210 (EN)  
**Creationdate :** 10.12.19 Version : 1.1  
**Replaces:** BDS002430\_20190325

Classification is based on test data.

**Health:** Eye irritation, category 2  
Causes serious eye irritation.  
Specific target organ toxicity - single exposure, category 3  
May cause drowsiness or dizziness.

Classification based on calculation method.

**Environment:** Not classified


Classification based on calculation method.

## 2.2. Label elements

### Labelling according to Regulation (EC) No 1272/2008

**Product identifier:** Contains:  
acetone; propan-2-one; propanone  
n-butyl acetate  
2-methoxy-1-methylethyl acetate

**Hazard pictogram(s):**



**Signal word:** Danger

**Hazard statement(s):** H222 : Extremely flammable aerosol.  
H229 : Pressurised container: May burst if heated.  
H319 : Causes serious eye irritation.  
H336 : May cause drowsiness or dizziness.

**Precautionary statement(s):** P102 : Keep out of reach of children.  
P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
P211 : Do not spray on an open flame or other ignition source.  
P251 : Do not pierce or burn, even after use.  
P261 : Avoid breathing dust/fume/gas/mist/vapours/spray.  
P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.  
P501-2 : Dispose of contents/container to an authorised waste collection point.

**Supplemental Hazard information:** Repeated exposure may cause skin dryness or cracking.

E : Explosif

## 2.3. Other hazards

No information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures



**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS002430\_3\_20191210 (EN)  
**Creationdate :** 10.12.19 Version : 1.1  
**Replaces:** BDS002430\_20190325

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
acetone; propan-2-one; propanone	01- 2119471330-49	67-64- 1	200- 662-2	25- 50	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	A
dimethyl ether	01- 2119472128-37	115- 10-6	204- 065-8	12.5- 20	Flam. Gas 1, Press. Gas	H220,H280	A
butane (<= 0,1 % butadiene)	01- 2119474691-32	106- 97-8	203- 448-7	5-10	Flam. Gas 1, Press. Gas	H220,H280	K
2-methoxy-1- methylethyl acetate	01- 2119475791-29	108- 65-6	203- 603-9	5-10	Flam. Liq. 3	H226	A
isobutane	01- 2119485395-27	75-28- 5	200- 857-2	2.5-5	Flam. Gas 1, Press. Gas	H220,H280	K
Cellulose nitrate		9004- 70-0	-	2.5-5	-	-	
n-butyl acetate	01- 2119485493-29	123- 86-4	204- 658-1	10- 12.5	Flam. Liq. 3, STOT SE 3	H226,H336	
propane	01- 2119486944-21	74-98- 6	200- 827-9	10- 12.5	Flam. Gas 1, Press. Gas	H220,H280	B
xylene	01- 21194488216- 32	1330- 20-7	215- 535-7	<2.5	Flam. Liq. 3, Acute Tox. 4, Acute Tox. 4, Skin Irrit. 2, Eye Irrit. 2, STOT SE 3, STOT RE 2, Asp. Tox. 1	H226,H312,H332,H315,H319,H335,H373,H304	A,W
ethanol; ethyl alcohol	01- 2119457610-43	64-17- 5	200- 578-6	<2.5	Flam. Liq. 2, Eye Irrit. 2	H225,H319	B,X,W

**Explanation notes**

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

W : Note: substance mentioned on the list of CMR-substances of the Dutch Ministry of Social Affairs and Employment (SZW)

X : SCL (specific concentration limit)in accordance with art.10 of CLP Regulation No 1272/2008

(\* Explanation phrases : see chapter 16)

**SECTION 4: First aid measures****4.1. Description of first aid measures**

<b>Contact with eyes :</b>	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
<b>Contact with skin :</b>	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	If swallowed accidentally, do not induce vomiting and seek medical advice.

**4.2. Most important symptoms and effects, both acute and delayed**

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
---------------------	--



**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS002430\_3\_20191210 (EN)  
**Creationdate :** 10.12.19 Version : 1.1  
**Replaces:** BDS002430\_20190325

**Ingestion :** May cause gastrointestinal disturbances  
Symptoms : sore throat, abdominal pain, nausea, vomiting

**Skin contact :** May cause irritation.  
Symptoms : redness and pain

**Eye contact :** Irritating to eyes  
Symptoms : redness and pain

#### 4.3. Indication of any immediate medical attention and special treatment needed

**General Advice :** If you feel unwell, seek medical advice (show the label where possible)  
If symptoms persist always call a doctor

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

#### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

#### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

#### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

#### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

#### 6.4. Reference to other sections



**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS002430\_3\_20191210 (EN)

**Creationdate :** 10.12.19 Version : 1.1  
**Replaces:** BDS002430\_20190325

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
 Take precautionary measures against static discharges  
 Equipment should be earthed  
 Use explosion-proof electrical/ventilating/lighting/.../equipment.  
 Use only non-sparking tools.  
 Do not breathe aerosols or vapours.  
 Ensure adequate ventilation  
 Avoid contact with skin and eyes.  
 Wash thoroughly after use  
 Wear protective gloves/protective clothing/eye protection/face protection.  
 Eyewash bottles should be available

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
 Keep out of reach of children.

### 7.3. Specific end use(s)

Paints

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
2-methoxy-1-methylethyl acetate	108-65-6	TWA	50 ppm
		STEL	100 ppm
dimethyl ether	115-10-6	TWA	1000 ppm
xylene	1330-20-7	TWA	50 ppm
		STEL	100 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
<b>National established exposure limits, United Kingdom</b>			
butane (<= 0,1 % butadiene)	106-97-8	TWA	600 ppm
		STEL	750 ppm
2-methoxy-1-methylethyl acetate	108-65-6	TWA	50 ppm
		STEL	100 ppm
dimethyl ether	115-10-6	TWA	400 ppm



**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS002430\_3\_20191210 (EN)  
**Creationdate :** 10.12.19 Version : 1.1  
**Replaces:** BDS002430\_20190325

		STEL	500 ppm
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm
xylene	1330-20-7	TWA	50 ppm
		STEL	100 ppm
ethanol; ethyl alcohol	64-17-5	TWA	1000 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
		STEL	1500 ppm
<b>National established exposure limits, Ireland</b>			
butane (<= 0,1 % butadiene)	106-97-8	TWA	1000 ppm
2-methoxy-1-methylethyl acetate	108-65-6	TWA	50 ppm
		STEL	100 ppm
dimethyl ether	115-10-6	TWA	1000 ppm
		STEL	-
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm
xylene	1330-20-7	TWA	50 ppm
		STEL	100 ppm
ethanol; ethyl alcohol	64-17-5	STEL	1000 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
		STEL	-
propane	74-98-6	TWA	1000 ppm

## 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation Wear suitable protective gloves
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	(filter AXP2)
<b>hands and skin :</b>	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	(butyl rubber)
<b>eyes :</b>	Wear safety eyewear according to EN 166.
<b>Environmental protection:</b>	Avoid release to the environment. Collect spillage.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

**Appearance : physical state :** Liquid under pressure.



**CRC Industries Europe bvba**

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

6 / 11

**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS002430\_3\_20191210 (EN)  
**Creationdate :** 10.12.19 Version : 1.1  
**Replaces:** BDS002430\_20190325

**colour :** See color cap.  
**odour :** Characteristic odor.  
**pH :** Not applicable.  
**Boiling point/range :** Not available.  
**Flash point :** < 0 °C  
**Evaporation rate :** Not available.  
**Explosion limits : upper limit :** 26.2 %  
**lower limit :** 1.2 %  
**Vapour pressure :** 830 kPa (@ 20°C).  
**Relative density :** 0.87 g/cm<sup>3</sup> (@ 20°C).  
**Solubility in water :** Not available.  
**Auto-ignition :** Not determined.  
**Viscosity :** Not applicable.

## 9.2. Other information

**VOC = volatile organic compounds** 779 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO<sub>2</sub>

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects



Productname : ACRYLIC PAINT      Creationdate : 10.12.19 Version : 1.1  
 Ref.Nr.: BDS002430\_3\_20191210 (EN)      Replaces: BDS002430\_20190325

**acute toxicity:** based on available data the classification criteria are not met  
**skin corrosion/irritation:** based on available data the classification criteria are not met  
**serious eye damage/irritation:** Causes serious eye irritation.  
**respiratory or skin sensitisation:** based on available data the classification criteria are not met  
**germ cell mutagenicity:** based on available data the classification criteria are not met  
**carcinogenicity:** based on available data the classification criteria are not met  
**toxicity for reproduction:** based on available data the classification criteria are not met  
**STOT-single exposure:** May cause drowsiness or dizziness.  
**STOT repeated exposure:** based on available data the classification criteria are not met  
**aspiration hazard:** based on available data the classification criteria are not met

#### Information on likely routes of exposure:

**Inhalation :** Inhalation of solvent vapours may give rise to nausea, headaches and dizziness  
**Ingestion :** May cause gastrointestinal disturbances  
**Skin contact :** May cause irritation.  
**Eye contact :** Irritating to eyes

#### Toxicological data :

Hazardous ingredient	CAS-nr.	method	
2-methoxy-1-methylethyl acetate	108-65-6	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	10.8 mg/l
		LD50 derm.rat	> 5000 mg/kg
		LD50 derm.rabit	> 5000 mg/kg
dimethyl ether	115-10-6	LC50 inhal.rat	309 mg/l
n-butyl acetate	123-86-4	LD50 oral rat	10760 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 1400 mg/kg
ethanol; ethyl alcohol	64-17-5	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rabit	> 2000 mg/kg
acetone; propan-2-one; propanone	67-64-1	LD50 oral rat	> 5800 mg/kg
		LC50 inhal.rat	76 mg/l
		LD50 derm.rabit	> 15800 mg/kg

## SECTION 12: Ecological information

### 12.1. Toxicity

Not classified

#### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method
----------------------	---------	--------



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com



**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS002430\_3\_20191210 (EN)

**Creationdate :** 10.12.19 Version : 1.1  
**Replaces:** BDS002430\_20190325

2-methoxy-1-methylethyl acetate	108-65-6	LC50 fish	100-180 mg/l
		EC50 daphnia	> 400 mg/l
dimethyl ether	115-10-6	IC50 algae	154.9 mg/l
		LC50 fish	4.1 mg/l
		EC50 daphnia	4.4 mg/l
n-butyl acetate	123-86-4	IC50 algae	647 mg/l
		LC50 fish	18 mg/l
		EC50 daphnia	44 mg/l
ethanol; ethyl alcohol	64-17-5	LC50 fish	> 100 mg/l
acetone; propan-2-one; propanone	67-64-1	IC50 algae	530 mg/l
		LC50 fish	5540 mg/l
		EC50 daphnia	8800 mg/l

## 12.2. Persistence and degradability

No experimental data available

## 12.3. Bioaccumulative potential

No experimental data available

## 12.4. Mobility in soil

No experimental data available

## 12.5. Results of PBT and vPvB assessment

No information available

## 12.6. Other adverse effects

No experimental data available  
 GWP (global warming potential): 1

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**Product :** 15 01 00, 15 01 04  
**Contaminated packaging :** 08 01 00, 08 01 11  
**National regulations :** Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : 1950



Productname : ACRYLIC PAINT      Creationdate : 10.12.19 Version : 1.1  
Ref.Nr.: BDS002430\_3\_20191210 (EN)      Replaces: BDS002430\_20190325

**14.2. UN proper shipping name**

Proper shipping name: AEROSOLS

**14.3. Transport hazard class(es)**

Class: 2.1  
ADR/RID - Classification code: 5F

**14.4. Packing group**

Packing group: Not applicable.

**14.5. Environmental hazards**

ADR/RID - Environmentally  
hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally  
hazardous: No

**14.6. Special precautions for user**

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203

**14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code**

Not applicable.

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

**15.2. Chemical safety assessment**

No information available

**SECTION 16: Other information**

Productname : ACRYLIC PAINT

Creationdate : 10.12.19 Version : 1.1

Ref.Nr.: BDS002430\_3\_20191210 (EN)

Replaces: BDS002430\_20190325

\*Explanation hazard statements: - : -

H220 : Extremely flammable gas.

H225 : Highly flammable liquid and vapour.

H226 : Flammable liquid and vapour.

H280 : Contains gas under pressure; may explode if heated.

H304 : May be fatal if swallowed and enters airways.

H312 : Harmful in contact with skin.

H315 : Causes skin irritation.

H319 : Causes serious eye irritation.

H332 : Harmful if inhaled.

H335 : May cause respiratory irritation.

H336 : May cause drowsiness or dizziness.

H373 : May cause damage to organs through prolonged or repeated exposure

acronyms and synonyms:

TWA = time weight average

STEL = short time exposure limit

VOC = volatile organic compounds

PBT = persistent bioaccumulative toxic

vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.