

Product datasheet

Specifications



APC Smart-UPS X, Line Interactive, 3kVA, Rack/tower convertible 4U, 208V-230V, 8x C13+2x C19 IEC, SmartSlot, Extended runtime, Short depth

SMX3000HV

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Product or component type	Uninterruptible power supply (UPS)
---------------------------	------------------------------------

Complementary

Communication port type	SmartSlot
-------------------------	-----------

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery type	Lead-acid battery
Extended runtime	1
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h
Number of battery replacement quantity	1
Battery life	3...5 year(s)
Battery charger power	245 W rated

General

Provided equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable User manual USB cable Rack mounting brackets
Number of power module	0
Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	Extended run

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Redundant	No
Physical	
Number of rack unit	4U
Cable length	1.8 m
Number of cables	1
Colour	Black
Height	43.2 cm
Width	17.8 cm
Depth	48.3 cm
Net weight	38.64 kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	1
USB compatible	Yes
Input	
Main Input Voltage	208 V 230 V
Other Input Voltage	220 V 240 V
Input Connection Type	IEC 320 C20 Schuko CEE 7 / EU1-16P BS1363A British
Input voltage limits	140...280 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Output	
Main Output Voltage	230 V
Other Output Voltage	208 V 220 V 240 V
Rated power in W	2700 W
rated power in VA	3000 VA
output connection type	8 IEC 320 C13 2 IEC Jumpers 2 IEC 320 C19
Crest factor	3 : 1
Harmonic distortion	Less than 5 %
Maximum configurable power in VA	3000 VA
Maximum configurable power in W	2700 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave

Output frequency	50/60 Hz +/- 3 Hz sync to mains
------------------	---------------------------------

Conformance

Product certifications	CE EAC IRAM RCM TISI VDE UK PSTI
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic level	55 dBA
Heat dissipation	184 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.0000000000...15240.0000000000 m
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

control panel	Multifunction LCD status and control console
Emergency power off	Yes
Free slots	1
Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rate	645 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	33.000 cm
Package 1 Width	59.500 cm
Package 1 Length	64.500 cm
Package 1 Weight	47.630 kg
Unit Type of Package 2	P12
Number of Units in Package 2	6
Package 2 Height	114.000 cm

Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	297.780 kg
Pallet unit layers	2
Pallet layers	4

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available
----------	--

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	2448
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	5ee38369-4dfb-4636-ab65-b08aa3242891
REACH Regulation	REACH Declaration

Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes