



Wire Protection & Management > Heat Shrink Shapes > Heat Shrink Caps



Wall Type: **Single Wall**  
Material Code: **25**  
Material Systems Code: **25**  
Adhesive Requirement: **Adhesive Purchased Separately**  
Operating Temperature Range: **-75 – 150 °C [-103 – 302 °F]**

Features

Product Type Features

Wall Type	Single Wall
-----------	-------------

Configuration Features

Adhesive Requirement	Adhesive Purchased Separately
----------------------	-------------------------------

Body Features

Shrink Ratio	2:1
Primary Product Color	Black
Flexibility	Flexible
Primary Product Material	Crosslinked Polyolefin
Sealant Type	None
Material Code	25
Material Systems Code	25

Dimensions

Recovered Wall Thickness (Nominal)	2.54 mm[.1 in]
Product Length	91 mm[3.6 in]
Wall Thickness	Medium
Recovered Inside Diameter (Max)	18 mm[.71 in]
Expanded Inside Diameter (Min)	39.4 mm[1.55 in]

Usage Conditions

--



Flammability Performance	Flame-Retardant
Resistance Properties	Immersion Protection
Resistance Protection	Suitable for long term fluid exposure at elevated temperatures
Operating Temperature Range	-75 – 150 °C[-103 – 302 °F]

Other

Molded Part Shape Code	101A
Size Code	73

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 657863-000  
[S1125-KIT-8](#)


Customers Also Bought




TE Part #234063-E  
[STVROL BUT 500 CSI 2026 207 \\* AL J 2 340](#)




TE Part #813789-000  
[202A163-3-0](#)




TE Part #32151  
[SPLICE,SOLIS BUTT 12-10](#)



TE Part #5-749877-7  
[68 50SR PANEL MOUNT RCPT, ROHS](#)



TE Part #631516-000  
[202K121-100/180-0](#)



TE Part #902973-000  
[DK-621-0411-P](#)



TE Part #CV25382001  
[RW-175-E-3/32-X-STK](#)



TE Part #5749197-1  
[100 50SR KIT,ST,UK](#)



TE Part #5070072039  
[RNF-100-3/8-X-STK](#)



TE Part #5053182032  
[RNF-100-3/8-9-STK](#)

Documents

Product Drawings

[101A073-25-0](#)

English

Datasheets & Catalog Pages

[1654025\\_Sec4\\_-25](#)

English

[1654025\\_Sec4\\_101A011to094](#)

English



Raychem Molded Parts Visual Guide

English

Product Specifications

Product Specification

English