



COMBICLICK backing pad dia. 115/125 mm thread M14 for angle grinders 115 and 125

**COMBICLICK backing pad dia. 115/125 mm thread M14 for
angle grinders 115 and 125**

Item number: [44890150](#)

EAN: [4007220725764](#)

With this backing pad, COMBICLICK tools can be used on commercially available angle grinders.

The COMBICLICK system consists of a specially developed backing pad and a rugged mounting system at the back of the tool. The unique geometry of the cooling slots ensures high air throughput, which in turn considerably reduces the thermal load on the abrasive material and the workpiece. Compared with conventional tools, the quick-mounting system, robust holder, secure tool-locking feature and integrated cooling system together achieve a workpiece temperature that is 30 % lower, a 25 % higher stock removal rate, a 30 % longer tool life, and better utilization of the abrasive material.

Hardness CC-GT (medium) = black

Technical information

Dia. thread	M14
Max. RPM	13300 RPM
PFERD TOOLS type	CC-GT 115-125
Suitable for	Angle grinders 115 / 125, spindle M14
Suitable for diameter [mm]	115, 125
Version	medium

Advantages

- ✓ The geometry of the cooling slots significantly reduces the thermal load.
- ✓ High economic efficiency due to minimal tool change times.
- ✓ The innovative quick-mounting system ensures convenient handling and rapid tool changing.

Recommendations for use

- ✓ Type CC-H-GT is mainly used to work on stainless steel (INOX). It has a very high edge strength, which enables a higher contact pressure.

Safety notes

- ✓ The maximum permitted peripheral speed is 80 m/s.
- ✓ For safety reasons, the maximum permitted rotational speed indicated must never be exceeded.

Drive types

- ✓ Angle grinder
 - ✓ Cordless angle grinder
-

**PFERD
TOOLS**



August Rüggeberg GmbH & Co. KG
Hauptstraße 13
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

info@pferd.com