

OYA1360-50-4-20-P-1

Technical drawing of a 12V/20Ah battery, showing front, side, and detail views with dimensions in mm.

Front View (Left): Shows the battery terminals. The top terminal is labeled 'T' and the bottom terminal is labeled '1'. The overall length is indicated as 'L'.

Side View (Top): Shows the battery profile. The top terminal is labeled 'R'. Dimensions include a total length of 61,5 mm, a distance of 29,5 mm from the bottom to the center of the terminal, and a terminal width of 11 mm. The bottom terminal is labeled 'M12x1'.

Detail View (Bottom): Shows a close-up of the bottom terminal, labeled '2' and '3'. It features a width of 28 mm and a height of 30 mm.

Top View (Right): Shows the battery from above. The overall width is 14,5 mm. The distance between the two main terminals is 40 mm, with a 20 mm gap between them. The terminal width is 10 mm. The bottom terminal is labeled 'M5' and has a width of 1,5 mm.

Bottom View (Bottom): Shows the battery from below. The overall width is 28 mm. The distance between the two main terminals is 40 mm, with a 20 mm gap between them. The terminal width is 10 mm. The bottom terminal is labeled 'Ø5,5'.

- | | |
|---|---------------------------------------|
| T | transmitter |
| R | receiver |
| 1 | LED three-colour red / green / orange |
| 2 | LED 2-colour yellow/blue |
| 3 | LED 2-colour red/green |



Type of light	infrared light
Electrical design	PNP
Protection	IP 65; IP 67

Protective function	access prevention bodies or parts of bodies
---------------------	---



Safety light curtain

OYA1360-50-4-20-P-1

Electrical data		
Operating voltage tolerance	[%]	20
Operating voltage	[V]	24 DC
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	< 2
Type of light		infrared light
Wave length	[nm]	950
Receiver		
Current consumption	[mA]	83
Transmitter		
Current consumption	[mA]	42
Outputs		
Electrical design		PNP
Number of OSSD outputs		2
Max. current load per OSSD output	[mA]	400; (24 V)
Short-circuit protection		yes
Detection zone		
Protected area height	[mm]	1360
Resolution (detection capacity d)	[mm]	50
Protection area width (low light intensity)	[m]	0...10
Protection area width (high light intensity)	[m]	3...20
Response times		
Response time	[ms]	6.5
Operating conditions		
Applications		class C to EN 60654-1 weatherproof application
Ambient temperature	[°C]	-10...55
Max. relative air humidity	[%]	95
Protection		IP 65; IP 67
Tests / approvals		
EMC	IEC 61496-1	
Shock resistance	IEC 61496-1	
Vibration resistance	IEC 61496-1	
Safety classification		
ESPE type (IEC 61496-1)		4
Complies with the requirements	ISO 13849-1: 2015 category 4, PL e	
	IEC 61508 SIL 3	
	IEC 62061 SIL 3	
Mission time TM	[h]	175200
PFH	[1/h]	1,4E-08

OY289S



Safety light curtain

OYA1360-50-4-20-P-1


Mechanical data		
Weight	[g]	4705
Dimensions	[mm]	1413 x 28 x 30
Materials		housing: aluminium; front pane: PC
Length L	[mm]	1413
Displays / operating elements		
Display		LED, yellow
		LED, green
		LED, red
		LED, blue
		LED, orange
Accessories		
Items supplied		mounting bracket: 6
		slot nuts: 6
		Nuts
Remarks		
Pack quantity		1 pcs.

Electrical connection - receiver

Connector: 1 x M12; coding: A; Maximum cable length: 100 m; for wire cross-section 0.34 mm²



Connection



Safety light curtain

OYA1360-50-4-20-P-1

Electrical connection - transmitter

Connector: 1 x M12; coding: A



Connection

