## SIEMENS

## Data sheet

## 3SE5112-0LD02



Position switch Metal enclosure 40 mm according to EN 50041, Device connection 1x (M20 x 1.5) 1 NO/2 NC quick action contacts, roller plunger with 3 mm overtravel and stainless steel roller 13 mm

product brand name	SIRIUS	
product designation	Mechanical position switches	
product type designation	3SE5	
manufacturer's article number		
<ul> <li>of the supplied basic switch</li> </ul>	<u>3SE5112-0LA00</u>	
<ul> <li>of the supplied actuator head for position switches</li> </ul>	<u>3SE5000-0AD02</u>	
<ul> <li>of the supplied switching contacts</li> </ul>	<u>3SE5000-0LA00</u>	
<ul> <li>of the supplied empty enclosure with cover</li> </ul>	<u>3SE5112-0AA00</u>	
suitability for use safety switch	Yes	
General technical data		
product function positive opening	Yes	
insulation voltage rated value	400 V	
degree of pollution	class 3	
surge voltage resistance rated value	6 kV	
protection class IP	IP66/IP67	
shock resistance		
<ul> <li>according to IEC 60068-2-27</li> </ul>	30g / 11 ms	
vibration resistance according to IEC 60068-2-6	0.35 mm/5g	
mechanical service life (operating cycles) typical	15 000 000	
electrical endurance (operating cycles) at AC-15 at 230 V typical	100 000	
thermal current	10 A	
material of the enclosure of the switch head	metal	
reference code according to IEC 81346-2	В	
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A	
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A	
continuous current of the DIAZED fuse link gG	6 A	
active principle	mechanical	
repeat accuracy	0.05 mm	
Substance Prohibitance (Date)	07/01/2006	
minimum actuating force in directions of actuation	20 N	
length of the sensor	116.3 mm	
width of the sensor	40 mm	
Ambient conditions		
ambient temperature		
during operation	-25 +85 °C	
<ul> <li>during storage</li> </ul>	-40 +90 °C	
explosion protection category for dust	none	
design of the switching contact	mechanical	
operating frequency rated value	50 60 Hz	

number of NC contacts for auxiliary contacts	2	
number of NO contacts for auxiliary contacts	1	
operational current at AC-15		
• at 24 V rated value	6 A	
• at 125 V rated value	6 A	
<ul> <li>at 240 V rated value</li> </ul>	6 A	
<ul> <li>at 400 V rated value</li> </ul>	4 A	
operational current at DC-13		
at 24 V rated value	3 A	
• at 125 V rated value	0.55 A	
at 250 V rated value	0.27 A	
at 250 V rated value     at 400 V rated value	0.12 A	
	0.12 A	
Enclosure		
design of the housing	block, narrow	
material of the enclosure	metal	
coating of the enclosure	cathodic dip coating	
design of the housing according to standard	Yes	
Drive Head		
design of the actuating element	Roller plunger, high-grade steel roller	
standard-compliant actuator head	EN 50041, design C	
shape of the switch head	roller	
design of the switching function	positive opening	
circuit principle	snap-action contacts	
number of switching contacts safety-related	2	
cable entry type	1x (M20 x 1.5)	
Installation/ mounting/ dimensions		
mounting position	any	
fastening method	screw fixing	
Connections/ Terminals	Solew lixing	
type of electrical connection	screw-type terminals	
type of connectable conductor cross-sections		
• solid	1x (0.5 1.5 mm <sup>2</sup> ), 2x (0.5 0.75 mm <sup>2</sup> )	
finely stranded with core end processing	1x (0.5 1.5 mm <sup>2</sup> ), 2x (0.5 0.75 mm <sup>2</sup> )	
for AWG cables solid	1x (20 16), 2x (20 18)	
for AWG cables stranded	1x (20 16), 2x (20 18)	
design of the interface for safety-related communication	without	
Communication/ Protocol		
design of the interface	without	
Certificates/ approvals		
General Product Approval		Functional Safety/Safety of Ma- chinery
		Type Examination Cer- tificate
Declaration of Conformity Test Certif	ficates other	
Declaration of Comonnity Test Certif	licates other	
UK CE ates/Tes ates/Tes		
Further information		

Siemens has decided to exit the Russian market (see here). https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

https://support.industry.siemens.com/cs/ww/en/view/109813875

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5112-0LD02


Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5112-0LD02

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5112-0LD02

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3SE5112-0LD02&lang=en





last modified:

1/26/2022 🖸