




SR-LC

LARGE SOCKET ROLL

- HIGHLY DURABLE 600D POLYESTER EXTERNAL CONSTRUCTION
- WATER-RESISTANT AND WIPEABLE INTERNAL CONSTRUCTION
- EXTERNAL CARRYING HANDLE
- EXTERNAL ZIPPERED POCKET
- ADJUSTABLE DUAL-BUCKLE FASTENING SYSTEM
- ACCOMMODATES BOTH METRIC (5/32IN UP TO 3/4IN) AND SAE (4MM UP TO 17MM) SOCKETS
- 2 ROWS OF 15 ELASTIC SOCKET STORAGE LOOPS OF VARIOUS SIZES
- 2 RAILS OF TUBING FOR ADDED SECURITY OF SOCKETS WHEN STORED IN THE LOOPS
- 2 CENTER ROWS OF 5 ELASTIC LOOP FOR STORING SOCKET WRENCHES AND EXTENSIONS
- FLAPS ALONG THE PERIMETER THAT FOLD INWARD TO PREVENT ITEMS FROM FALLING OUT
- EXTERNAL VELCRO LOOP FOR ATTACHING TO THE INSIDE OF THE TR-LC
- YKK® ZIPPERS



DIM: 16.5" H X 13" W
(42cm H X 33cm W)


WT: 0.9 LBS
(0.4 KG)

MAX PAYLOAD: 10 LBS
(4.5 KG)

SECURING FLAPS

CARRYING HANDLE

CENTER ELASTIC STORAGE ROWS FOR SOCKET WRENCHES AND EXTENSIONS



ELASTIC STORAGE ROWS FOR SOCKETS
(both metric and standard)



INCLUDED AND COMPATIBLE WITH TR-LC