

Productname : AMBERKLENE FE10
Ref.Nr.: UDS000445_3_20170224 (EN)

Creationdate : 24.02.17 Version : 1.0
Replaces: UDS000445_20150330

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

AMBERKLENE FE10
Bulk

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Heavy duty

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.
Ambersil House - Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom
Tel.: +44 1278 727200
Fax.: +44 1278 425644
E-mail : hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical:	Flammable liquid, category 2 Highly flammable liquid and vapour.
Health:	Aspiration Hazard Category 1 May be fatal if swallowed and enters airways. Skin irritation, category 2 Causes skin irritation.
Environment:	Specific target organ toxicity - single exposure, category 3 May cause drowsiness or dizziness.
Other hazards :	Hazardous to the aquatic environment, chronic category 2 Toxic to aquatic life with long lasting effects.

2.2. Label elements



Productname : AMBERKLENE FE10
 Ref.Nr.: UDS000445_3_20170224 (EN)

Creationdate : 24.02.17 Version : 1.0
 Replaces: UDS000445_20150330

Labelling according to Regulation (EC) No 1272/2008

Product identifier:	Contains: Hydrocarbons, C7-C8, cyclics Hydrocarbons, C6-C7, n-alkanes,isoalkanes,cyclics,< 5% n-hexane
Hazard pictogram(s):	   
Signal word:	Danger
Hazard statement(s):	H225 : Highly flammable liquid and vapour. H304 : May be fatal if swallowed and enters airways. H315 : Causes skin irritation. H336 : May cause drowsiness or dizziness. H411 : Toxic to aquatic life with long lasting effects.
Precautionary statement(s):	P101 : If medical advice is needed, have product container or label at hand. P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P271 : Use only outdoors or in a well-ventilated area. P301/310 : IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician. P331 : Do NOT induce vomiting. P405 : Store locked up. P501-2 : Dispose of contents/container to an authorised waste collection point.

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons, C7-C8, cyclics	01-2119486992-20	-	927-033-1	30-60	Flam. Liq. 2, Asp. Tox. 1, Skin Irrit. 2, STOT SE 3, Aquatic Chronic 2	H225,H304,H315,H336,H411	
methylal	01-2119664781-31	109-87-5	203-714-2	10-30	Flam. Liq. 2	H225	B
Hydrocarbons, C6-C7, n-alkanes,isoalkanes,cyclics,< 5% n-hexane	01-2119475514-35	64742-49-0	921-024-6	10-30	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225,H315,H336,H304,H411	B

Productname : AMBERKLENE FE10
 Ref.Nr.: UDS000445_3_20170224 (EN)

Creationdate : 24.02.17 Version : 1.0
 Replaces: UDS000445_20150330

n-hexane	110-54-3	203-777-6	<3	Flam. Liq. 2, Repr. 2, Asp. Tox. 1, STOT RE 2, Skin Irrit. 2, STOT SE 3, Aquatic Chronic 2	H225,H361f,H304,H373,H315,H336,H411 A
----------	----------	-----------	----	--	---------------------------------------

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with water for at least 15 minutes Seek medical attention if irritation persists
Contact with skin :	Remove contaminated clothing immediately and wipe affected skin with dry cloth. Then wash with soap and water Seek medical attention if irritation persists
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	Irritating to skin Symptoms : redness and pain
Eye contact :	Mildly irritating to eyes Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture



Productname : AMBERKLENE FE10
Ref.Nr.: UDS000445_3_20170224 (EN)

Creationdate : 24.02.17 Version : 1.0
Replaces: UDS000445_20150330

May form explosive vapour/air mixtures
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing including eye/face protection.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Place in appropriate container
This material and/or its container must be disposed of as hazardous waste.

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Keep container tightly closed, in a cool, well ventilated place.

Productname : AMBERKLENE FE10
Ref.Nr.: UDS000445_3_20170224 (EN)

Creationdate : 24.02.17 Version : 1.0
Replaces: UDS000445_20150330

Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Heavy duty

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
n-hexane	110-54-3	TWA	20 ppm
National established exposure limits, United Kingdom			
methylal	109-87-5	TWA	1000 ppm
		STEL	1250 ppm
n-hexane	110-54-3	TWA	20 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product.
inhalation :	Ensure adequate ventilation In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equiped with organic gas/vapor cartridge (type AX)
hands and skin :	Wear suitable protective gloves
Recommended gloves:	Nitrile
eyes :	Wear safety goggles according to EN 166.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Apperance : physical state :	Liquid.
colour :	Colorless.
odour :	Solvent.
pH :	Not applicable.
Boiling point/range :	42 °C
Flash point :	- 6 °C
Evaporation rate :	Not available.
Explosion limits : upper limit :	17.6 %
lower limit :	0.7 %



Productname : AMBERKLENE FE10
Ref.Nr.: UDS000445_3_20170224 (EN)

Creationdate : 24.02.17 Version : 1.0
Replaces: UDS000445_20150330

Relative density : 0.767 g/cm3 (@ 20°C).
Solubility in water : Insoluble in water
Auto-ignition : > 200 °C
Viscosity : Not available.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Information on likely routes of exposure:

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact : Irritating to skin
Eye contact : May cause irritation.

Toxicological data :



Productname : AMBERKLENE FE10
Ref.Nr.: UDS000445_3_20170224 (EN)**Creationdate :** 24.02.17 Version : 1.0
Replaces: UDS000445_20150330

Hazardous ingredient	CAS-nr.	method	
methylal	109-87-5	LD50 oral rat	6423 mg/kg
Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, < 5% n-hexane	64742-49-0	LD50 derm.rabit	> 5000 mg/kg
		LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 25000 mg/m3
		LD50 derm.rat	> 2000 mg/kg
Hydrocarbons, C7-C8, cyclics	-	LD50 oral rat	>5840 mg/kg
		LC50 inhal.rat	>23300 mg/m3
		LD50 derm.rat	>2920 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 2
Toxic to aquatic life with long lasting effects.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
methylal	109-87-5	LC50 fish	> 1000 mg/l
		EC50 daphnia	> 1000 mg/l
Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, < 5% n-hexane	64742-49-0	LC50 fish	> 10 mg/l
		EC50 daphnia	3 mg/l
Hydrocarbons, C7-C8, cyclics	-	IC50 algae	10 mg/l
		LC50 fish	3.6 mg/l
		EC50 daphnia	3 mg/l

12.2. Persistence and degradability

No information available

12.3. Bioaccumulative potential

No information available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No information available

Productname : AMBERKLENE FE10
Ref.Nr.: UDS000445_3_20170224 (EN)

Creationdate : 24.02.17 Version : 1.0
Replaces: UDS000445_20150330

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1993

14.2. UN proper shipping name

Proper shipping name: FLAMMABLE LIQUID, N.O.S. (hydrocarbons, dimethoxymethane)

14.3. Transport hazard class(es)

Class: 3
ADR/RID - Classification code: F1

14.4. Packing group

Packing group: II

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: Yes
IMDG - Marine pollutant: Marine pollutant
IATA/ICAO - Environmentally hazardous: Yes

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D/E)
IMDG - Ems: F-E, S-E
IATA/ICAO - PAX: 353
IATA/ICAO - CAO 364

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.



Productname : AMBERKLENE FE10
Ref.Nr.: UDS000445_3_20170224 (EN)

Creationdate : 24.02.17 Version : 1.0
Replaces: UDS000445_20150330

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.

EU-directive 99/45/EC

Regulation (EC) No 1272/2008 (CLP)

Regulation (EC) No 1907/2006 (REACH)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: H225 : Highly flammable liquid and vapour.

H304 : May be fatal if swallowed and enters airways.

H315 : Causes skin irritation.

H336 : May cause drowsiness or dizziness.

H361f : H361f

H373 : May cause damage to organs through prolonged or repeated exposure

H411 : Toxic to aquatic life with long lasting effects.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.