

Mini-IR Illuminator

Art. no. TVAC71200

Page 1 of 2



- IR-floodlight with 2 high power LEDs
- Photo sensor which reacts to residual light from 2 lux
- Range of up to 10 m
- 90° beam angle
- Mounted directly on the camera

More light – better images

In order to record clear images even in the dark, the cameras need (infrared) light. The mini IR illuminator provides cameras with the light they need to operate in pitch black conditions, with infrared light at a wavelength of 850 nm from 2 high power LEDs facilitating night time recording.

Multi-compatible, with automatic light adjustment

Mounted directly on the camera, the IR illuminator is suitable for both black/white and day/night cameras. Should light levels drop below approximately 2 lux, the illuminator's light sensor reacts, automatically switching the IR-LEDs. Depending on the light sensitivity of the camera, the IR illuminator operates at a range of up to 10 m with a beam angle of 90°.

Perfectly suited to outdoor use

The IR illuminator is protected against dust and spraying water (IP54 protection rating), meaning it can be used in sheltered outdoor areas within a temperature range of -20°C to +50°C, with a maximum power consumption of 4 watts.

Note on the product:

A 12 V DC power supply unit is required in order to put the product into operation (CCTV power supply unit, item no TV7616).

Mini-IR Illuminator

Art. no. TVAC71200

Page 2 of 2

Technical Data:

Dimensions	52 x 52 x 70 mm
Horizontal/vertical IR angle	90 °
Arming	<2 Lux lx
Number of LEDs	2
Mount	1/4" thread
Width	52 mm
Height	52 mm
Cable length	0,7 m
Length	70 mm
Power consumption	2,5 W

Max. operating temperature	50 °C
Min. operating temperature	-20 °C
Net weight	0,2 kg
Optical wavelength	850 nm
IP protection class	65
DC voltage supply	12 V
Power consumption	350 mA
LED type	Semi-discrete