

Product data sheet

Specifications



Repacked TV socket, New Unica, mechanism, 2 modules, male IEC 9.52 mm, IP20, anthracite

NU346254W



This repacked option saves 0.559 over the standard condition

Main

Range	New Unica
Product or component type	TV socket
Device application	Communication Media device support
Device presentation	Mechanism
TV socket type	Individual
Colour tint	Anthracite (RAL 7021)

Complementary

TV connector	Male IEC 9.52 mm
Path attenuation	1.5 dB TV signal5...2200 MHz
DC current flow	Yes
Number of modules	2 modules
Material	Thermoplastic ABS-UV stabilised: central plate
surface treatment	Untreated
Surface finish	Painted powder coated
Marking	Without marking
Device mounting	Flush
fixing mode	Clip-in
Depth	35.5 mm
Width	45 mm
Height	45 mm
Embedding depth	35.5 mm
resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IP degree of protection	IP20
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

IK degree of protection	IK01
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-25...55 °C
Standards	CE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	4.500 cm
Package 1 Length	4.500 cm
Package 1 Weight	46.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.108 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.6 kg CO2 eq.

Use Better



Materials and Substances

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Free of Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins