

8581-01

## Torque wrench DREMOMETER

Code	ETIM
2311267	EC002132
EAN	UNSPSC
4002805930786	27-11-17-15
Country of origin	eCl@ss
Germany	21-04-02-22
Customs tariff number	
82041100	



### Article description

- Use:
- Controlled screw tightening in the range of 600 - 1500 Nm
- For use in almost all industrial manufacturing areas
- Features:
- Classified according to DIN EN ISO 6789-2:2017 Type II Class A, incl. traceable test certificate, calibrated to a maximum permissible deviation of +/- 3 % and thus more precise than the +/- 4 % required by the standard
- 1" square drive with pin-locking mechanism DIN 3120 - B 25, ISO 1174
- Automatic short-path actuation with tactile impulse and audible signal
- Single scale with a scale division of 25 Nm
- Technical advantage/Function:
- Lightweight yet robust (as the housing is made of an aluminium alloy) and resilient, very workshop-friendly
- No inaccuracies whether used with both hands or held away from the handle (as for standard torque wrenches)
- Both the square drive and fulcrum are on an axis which ensures a high degree of user safety; can be extended to reduce the user's working load.
- Double-lever mechanism for maximum cutting performance
- Forged lever chain from our group own quality forge
- Maximum precision even when subjected to extreme continuous use
- Long life cycles and tool lives • Easy operation - fast and safe torque tightening

### Article parts list

Extension tube,8564-92

### Article information

Contents (Qty of pieces)	1	Trigger mechanism	Short path triggering
Net weight [kg]	10,8 kg	Precision +/-	+/- 3 %
Total length [mm]	932 mm	Direction of tightening	Right
Total width [mm]	60 mm	Fixed setting	no
Total height [mm]	71 mm	Test certificate	DIN EN ISO 6789-2:2017
Material	Aluminum alloy	Graduation	25
Standard	DIN 3120 - B 25 ISO 1174	Head height 1 [mm]	40 mm
Drive connector square (male)	1"	Width of head 1 [mm]	60,0 mm
Drive connector square (male)	25 mm	Torque wrench type	EK
Drive type/drive	Single square	Calibration length	1473 mm
Torque (min.) [N·m]	600 Nm	Graduation [n·m]	25 Nm
Torque (max.) [N·m]	1500 Nm	Distance housing - square drive	30 mm
Torque range (min./max.) [N·m]	600 Nm - 1500 Nm	Storage/Content	Box
Torque range (min./max.) [lbf·ft]	-	Length of extension tube 1	925 mm