

Chassis Supports


Chassis Supports:

Fix directly between front/rear 19" mounting angles to accept standard vented 'chassis tray' (order separately) or customers equipment.

Materials and Finish:

- 1.5mm steel, zinc plated, colour passivated.

Description	Depth	Part Number
Chassis runners (2off)	380	CR39
Chassis runners (2off)	444	CR45
Chassis runners (2off)	571	CR58
Chassis runners (2off)	627	CR62



Chassis Tray


Chassis Trays:

Ventilated tray with fixings to fit directly on chassis runners (order separately). Two depths, 230 or 455mm.

Materials and Finish:

- 1.5mm steel, zinc plated, colour passivated.

Description	Depth	Part Number
Chassis tray	230	USCT230
Chassis tray	455	USCT455



Cantilever Shelves


Cantilever Shelves:

Fit to front face of 19" mounting angles, with angles set at standard 19" width. Ideal for modems, hubs or other networking equipment.

Materials and Finish:

- 1.5mm steel, painted light grey

Description	Height 'U'	Depth	Part Number
19" Front Mounted	1	190	MS19
19" Front Mounted	2	400	MS40
19" Front Mounted	3	400	MS403



Sliding Keyboard Shelf

Sliding Keyboard Shelf:

Enables a standard keyboard to be used any 19" cabinet. Turntable Turntable permits a keyboard which is wider than 450m to be turned through 90° for storage. Universal mounting brackets fit uprights set between 450 & 750mm apart.

Features:

- Painted light grey
- Depth adjustable between 450 & 750mm
- Universal mounting fits any standard 19" cabinet

Description	Part Number
Sliding Keyboard Shelf	KT750

Shelving Compatibility Maxtrix for Access

•• Will fit, recommended

• Will fit

• Will fit, NOT recommended

x Will NOT fit

Part No.	Description	Shelf Depth mm	Rack Depth					3 into 2	19" upright spacing	
			675 mm	875 mm	915 mm	1000 mm	1200 mm		Min mm	Max mm
Fixed 4 Post										
35kg Load Rating (Uniformly Distributed)										
QRSV45	Quick Fit Shelf 19"	450	••	•	•	•	•	x	300	450
QRSV55	Quick Fit Shelf 19"	550	•	••	•	•	•	x	350	550
QRSV65	Quick Fit Shelf 19"	650	x	••	•	•	•	x	450	650
QRSV75	Quick Fit Shelf 19"	750	x	•	••	••	•	x	550	750
90kg Load Rating (Uniformly Distributed)										
QRSVFW45	Quick Fit Shelf Full Width (800W ONLY)	450	••	•	•	•	•	x	300	450
QRSVFW65	Quick Fit Shelf Full Width (800W ONLY)	650	x	••	•	•	•	x	450	650
QRSVFW75	Quick Fit Shelf Full Width (800W ONLY)	750	x	•	••	••	•	x	550	750
90kg Load Rating (Uniformly Distributed)										
HDASV45AS	Adjustable Depth 19"	450	••	•	•	•	•	x	450	700
HDASV55AS	Adjustable Depth 19"	550	•	••	•	•	•	x	550	800
HDASV65AS	Adjustable Depth 19"	650	x	••	••	••	•	x	650	900
HDASV75AS	Adjustable Depth 19"	750	x	•	••	••	••	x	750	1000
HDASVFW55AS	Adjustable Depth Full Width (800W ONLY)	550	•	••	•	•	•	x	550	700
HDASVFW65AS	Adjustable Depth Full Width (800W ONLY)	650	x	••	••	•	•	x	650	900
HDASVFW75AS	Adjustable Depth Full Width (800W ONLY)	750	x	•	••	••	•	x	750	1000
Sliding										
45kg Load Rating (Uniformly Distributed)										
LDATSV45	Adjustable Depth Sliding Shelf 19"	455	••	•	•	•	•	••	444	749
LDATSV55	Adjustable Depth Sliding Shelf 19"	555	•	••	•	•	•	•	444	812
LADASV70	Adjustable Depth Sliding Shelf 19"	705	x	••	••	••	•	•	444	940
35kg Load Rating (Uniformly Distributed)										
TFWSV45	Fixed Depth Sliding Shelf Full Width (800W ONLY)	450	••	•	•	•	•	x	450	450
95kg Load Rating (Uniformly Distributed)										
ASSFW580	Fixed Depth Sliding Shelf Full Width(Heavy Duty) (800W ONLY)	580	x	••	•	•	•	x	580	580
125 kg Load Rating (Uniformly Distributed)										
QRTSV45	Quick Fit Adjustable Depth Sliding Shelf 19"	450	••	•	•	•	•	•	363	513
QRTSV60	Quick Fit Adjustable Depth Sliding Shelf 19"	600	•	••	•	•	•	•	513	663
QRTSV75	Quick Fit Adjustable Depth Sliding Shelf 19"	750	x	••	••	••	•	•	663	813
QRTSVFW45	Quick Fit Adjustable Depth Sliding Shelf Full width (800W ONLY)	450	••	•	•	•	•	x	363	513
QRTSVFW60	Quick Fit Adjustable Depth Sliding Shelf Full width (800W ONLY)	600	•	••	•	•	•	x	513	663
QRTSVFW75	Quick Fit Adjustable Depth Sliding Shelf Full width (800W ONLY)	750	x	•	••	••	•	x	663	813
Cantilever										
35 kg Load Rating (Uniformly Distributed)										
MS19	1U	190	•	•	•	•	•	•	n/a	n/a
MS40	2U	400	•	•	•	•	•	•	n/a	n/a
MS403	3U	400	•	•	•	•	•	•	n/a	n/a
Keyboard										
35 kg Load Rating (Uniformly Distributed)										
KT750	Adjustable Depth		•	•	•	•	•	•	450	750

