



Part Number : [08500008](#)

Product Description : KK 396 Crimp Terminal 8818,
22-18 AWG, Reel, Brass Tin (Sn)

Series Number : 8818

Status : Active

Product Category : Crimp Terminals

Engineering Number : 8818-(P909)

Packaging Alternative : [08500023](#) (Bag)



Documents & Resources

Drawings

[008500008_sd.pdf](#)

[PK-2759-002-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-08-50-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	8818
Description	KK 396 Crimp Terminal 8818, 22-18 AWG, Reel, Brass Tin (Sn)
Application	Power, Wire-to-Board
Product Name	KK 396
UPC	800753617889

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.180/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.41mm max.
Wire Size (AWG)	18, 20, 22
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 22-18 AWG	<u>638280300</u>
Mini-Mac Applicator	<u>638881100</u>

This document was generated on Sep 22, 2025