

PRECISION DEBURRING AND COUNTERSINKING IN STEEL

PRO

- 1 Three 90-degree cutting edges for precise drilling in soft metal



BOSCH

PRO STEEL HSS COUNTERSINK DRILL BIT

PRO


- ▶ For precise deburring and countersinking in soft metal, eg when deburring, and enlarging the hole's sides for countersunk fasteners
- ▶ Highly efficient for construction workers and installers: Precision
- ▶ Designed for deburring and countersinking in steel
- ▶ Cylindrical shank compatible with three-jaw drill chucks



PRODUCT PROPERTIES					ORDERING INFORMATION				
Diameter mm	Step height	Total length mm	Shank diameter inch	Shank diameter mm	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number
6.0	M 3	48		6	P1c	1	1	107 150	2 608 597 500
8.0	M 4	48		8	P1h	1	1	085 687	2 608 596 664
10.0	M 5	40		8	P1h	1	1	085 694	2 608 596 665
12.0	M 6	40	1/4	8	P1c	1	1	059 770	2 608 596 371
16.0	M 8	43		8	P1c	1	1	059 787	2 608 596 372
20.0	M 10	45		8	P1c	1	1	059 794	2 608 596 373


BOSCH