




VAL-U-LOK

TE Internal #: 2238021-1
Power Contacts, Contact, 600 VAC, Gold / Pre-Tin, 22 – 18 AWG
Wire Size, .33 – .82 mm² Wire Size, Wire-to-Wire, Wire & Cable,
Crimp, Power, Socket
[View on TE.com >](#)

Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**
Operating Voltage: **600 VAC**
Contact Mating Area Plating Material: **Gold, Pre-Tin**
Wire Size: **.33 – .82 mm²**

Features

Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Mating Area Plating Material	Gold, Pre-Tin
Contact Current Rating (Max)	9 A
Contact Type	Socket
Contact Retention Within Housing	With
Mating Square Post Dimension	1.14 mm[.045 in]
Contact Base Material	Brass
Contact Mating Area Plating Material Thickness	2.54 µm[100 µin]
Wire Contact Termination Area Plating Thickness	2.54 µm[100 µin]
Wire Contact Termination Area Plating Material	Pre-Tin



Wire Contact Termination Area Plating Material Finish	Bright
Contact Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
Wire Insulation Support	Without

Dimensions

Wire Size	.33 – .82 mm²
Accepts Wire Insulation Diameter Range	1.5 – 3.1 mm[.06 – .122 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

Packaging Features

Packaging Method	Bag & Box
------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

			
TE Part # 1586055-1 VAL-U-LOK SKT BR SN 16AWG	TE Part # 794955-1 VAL-U-LOK PIN BR SN 22-18AWG	TE Part # 794956-1 VAL-U-LOK SKT BR SN 22-18AWG	TE Part # 794956-5 VAL-U-LOK SKT BR SN 18-22AWG
			
TE Part # 2238016-1 VAL-U-LOK PIN BR SN 18-22AWG	TE Part # 794956-2 VAL-U-LOK SKT BR AU 22-18AWG	TE Part # 2238022-1 VAL-U-LOK PIN BR SN 26-22 LP	TE Part # 2238017-1 VAL-U-LOK SKT BR SN 18-22AWG
			
TE Part # 2238020-1 VAL-U-LOK PIN BR TN 22-18 LP	TE Part # 2238023-1 VAL-U-LOK SKT BR SN 26-22 LP	TE Part # 794955-5 VAL-U-LOK PIN BR SN 22-18AWG	

Customers Also Bought





TE Part #1-480305-0
03P CMNL CAP HSG F/H NATL



TE Part #1-480303-0
03P CMNL PLUG HSG F/H NATL



TE Part #6-1393250-0
W28-XTBB-15=W28



TE Part #1969608-5
5P VAL-U-LOK TPA 22-18 AWG




TE Part #414946-1
PLUG ASSY,STR,SMB



TE Part #61117-1
CMNL SOK 20-14 TPBR



TE Part #1969612-4
4P FH PLUG VAL-U-LOK V0



TE Part #1969614-8
8P RCPT VAL-U-LOK V0



TE Part #1969570-8
ASSY,HDR,VERT,GWT,BOSSED,DUAL ROW, EP2.5

Documents

Product Drawings

VAL-U-LOK SKT BR SN 22-18 LP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2238021-1_A_c-2238021-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2238021-1_A_c-2238021-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2238021-1_A_c-2238021-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1-1773730-3 VAL-U-LOK Connectors with TPA Flyer

English