

All MULTILOCK, CONNECTOR HOUSING (145)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts





TE Part # CAT-SIGH262


Signal Header



TE Part # CAT-M9194-T273

MULTILOCK, RECEPTACLE AND TAB

Customers Also Bought




TE Part #2-520263-2

ULTRA-FAST 250 ASY REC 22-18 TPBR




TE Part #40524

RING TERMINAL 12-10 AWG TPBR




TE Part #521781-1

250 HSG. PL MKIII REC. 6.81mm 4P NAT



TE Part #521780-1

250 HSG. PL MKIII REC. 7.11mm 5P NAT



TE Part #353537-1

040-3 UNSEALED CONT.TAB(S)




TE Part #55678-2

TERM,PG RING 12-10 1/4




TE Part #2-323682-1

TERMINAL,PIDG R 16-14HD 1/4




TE Part #3-520140-2

ULTRA-FAST 250 ASY REC 16-14 AWG TPBR



TE Part #171725-1

MIC CAP 13P WIRE TO WIRE



TE Part #174045-2

040 MULTILOCK PLUG 12P

Documents

Product Drawings

I/O PLUG ASSY .040 16P

English

CAD Files

Customer View Model

ENG_CVM_CVM_175966-1_A.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_175966-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_175966-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[MULTILOCK Connector System](#)

English

Product Specifications

[Application Specification](#)

English

[Crimping .040 Series Receptacle Contact](#)

English

Instruction Sheets

[Customer Manual \(non U.S.\)](#)

Japanese

[.040 Series Multilock I/O Connector Mark II](#)

Japanese

[Customer Manual \(non U.S.\)](#)

Japanese

[.040 Series, Multilock I/O Connector, Mark II](#)

Japanese