

# Thalassa PHD outdoor heavy duty - aluminium cable gland plate - W750 D420

NSYPPC74HD

#### Main

Range	Thalassa	
Product or component type	Cable gland plate	
Accessory / separate part category	Cable management accessory	
Application	Outdoor heavy duty	
Application	Multi-purpose	
Nominal width of the housing	750 mm	
Nominal depth of the housing	420 mm	
Range compatibility	Thalassa Thalassa PHD	
Mounting location	Enclosure bottom	
Type of gland plate	Plain aluminium	
Device composition	fixing elements 1 plate gasket	
Quantity per set	Set of 1	
Material	Aluminium	

## Complementary

Surface finish	Brushed finish
Fixing mode	Tool less - screw type quarter-turn
Height	15 mm
Width	Nominal: 750 mm Real: 760 mm
Depth	Nominal : 420 mm
Thickness	3 mm

### **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	36.000 cm
Package 1 Length	57.000 cm
Package 1 Weight	1.378 kg
Unit Type of Package 2	PAL

Number of Units in Package 2	8
Package 2 Height	29.000 cm
Package 2 Width	45.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	11.024 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

### ☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

#### **Use Better**

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	B8d0fb33-5e43-4121-80bd-e0d068ed5eda

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No