

**BOSCH**

Invented for life

# Product data sheet

## Power tools for trade & industry

Cordless Rotary Hammer with SDS plus

### GBH 18V-21



Bosch quality within reach – cordless comfort and brushless power

#### The most important data

Battery voltage	18 V
Max. impact energy	2 J
Drilling dia. in concrete with hammer drill bits	4 - 21 mm

**Order number** 0 611 911 100[> More product information](#)

## Technical data

### Technical data

Max. impact energy	2 J
Impact rate at rated speed	0 – 5,100 bpm
Rated speed	0 – 1,800 rpm
Battery voltage	18 V
Weight excl. battery	2.4 kg
Tool holder	SDS plus
Tool dimensions (length)	325 mm

### Drilling range

Drilling dia. in concrete with hammer drill bits	4 - 21 mm
Opt. app. range in concrete with hammer drill bits	6 - 10 mm
Max. drilling diameter in metal	13 mm
Max. drilling diameter in wood	13 mm

## Noise/vibration information

### Hammer drilling in concrete

Vibration emission value ah	10 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### Chiselling

Vibration emission value ah	7 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



# Product data sheet

Power tools for trade & industry

## Advantages:

- - Powerful impact system with 2.0 J; three modes (drilling, hammer drilling, chiselling) ensure versatile use
- - Brushless motor reduces the need for maintenance and improves runtime per battery charge, less downtime and increased longevity
- - Good power-to-weight ratio with only 2.4 kg in weight; even capable enough for light chiselling applications

