



Terminals & Splices > Splices



Splice Type: **Butt Splice**

Wire Size: **13 – 15 mm²**

Sealable: **No**

Splice Features: **Sight Hole**

Features

Product Type Features

Splice Accessory Type	Splice
Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Product Weight	8.499 g
Splice Features	Sight Hole

Contact Features

	500 μin
Terminal Plating Material	Silver
Contact Base Material	Copper



Barrel Type	Closed
-------------	--------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Outside Diameter	9.37 mm[.369 in]
Wire Size	20800 – 33100 CMA
Barrel Inside Diameter	5.89 mm[.232 in]
Terminal Material Thickness	1.45 mm[.057 in]
Product Length	25.78 mm[1.015 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1490413-2 HYP10 SOLIS HD 8AWG NEST	 TE Part # 69217 HYP8/10 SOLIS 6AWG DIE SET	 TE Part # 600850 ROTO-CRIMP TOOL (ASI)	 TE Part # 1901002-1 INDENTER, SOLISTRAND
 TE Part # 48127 HYP8 SOLIS 6-2AWG INDENTER	 TE Part # 1490414-2 HYP10 SOLIS HD 6-4AWG INDENTER	 TE Part # 601075 BANTAM ROTA-CRIMP TOOL	 TE Part # 1901000-1 NEST #6
 TE Part # 48128 HYP8 SOLIS 6AWG NEST			

Customers Also Bought



TE Part #CAT-P592-R472
PIDG Radiation Resistant C Rings /Spades




TE Part #2-1625959-5
HB03RE 50M 1% 100PPM




TE Part #4-87456-9
04 MODIV HSG COMP DR .100CL




TE Part #CAT-AM7801-CH8172
AMPSEAL 16 Housings



TE Part #1208484001
NTFR-3/16-0-SP



TE Part #808981-000
202D121-3/42-0



TE Part #776493-1
SOC, SF, SIZE 16, 18-20 AWG, AU/SN



TE Part #2103171-1
SHIELD, CAP, HVA280-2PHM

Documents

Product Drawings

SPLICE,SOLIS BUTT 6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-324309-2_S.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-324309-2_S.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-324309-2_S.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English