

### **FEATURES**

- Robust construction
- 25 mm shaft
- 1 W power rating
- Single turn
- 285° rotation (mechanical angle)

RS PRO 1 Gang Rotary
Wirewound Potentiometer
with an 6.35 mm Dia. Shaft 10kΩ, ±10%, 1W Power
Rating, Linear, Panel

RS Stock No.: 842-7119



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



## **Product Description**

Brought to you by RS PRO, a series of rotary potentiometers suitable for various applications. Widely used within electronics, each model can be mounted within various devices or even on PCB applications. These particular models generally have a rotational life of 100,000 revolutions and will excel within audio or electronic uses. All models are highly reliable and excellent quality.

#### **General Specifications**

Potentiometer Type	Rotary
Maximum Resistance	10kΩ
Tolerance	±10%
Linearity	±1%
Number of Gangs	1
Number of Turns	1
Electrical Taper	Linear
Element Material	Wire wound
Actuator Type	Slotted Shaft
Applications	Audio control: Both linear, and rotary potentiometers, are used to control audio equipment for changing the loudness and other audio related signals.  Television: They are used to control the picture brightness, colour response and contrast.  Motion control: In order to create a closed-loop control, potentiometers are used as position feedback devices known as a servomechanism.  Transducers: As these give large output signals, they find applications in designing of displacement transducers



# **Electrical Specifications**

Power Rating	1W
Termination Style	Solder
Dielectric Strength	500VAC
Insulation Resistance	1000Mohm
Maximum Resistance	10kΩ

## **Mechanical Specifications**

Dimension	25 4mm (dia ) v 40 5mm
Dilliension	25.4mm (dia.) x 40.5mm
Product Diameter	25.4mm
Product Length	40.5mm
Shaft Length	25mm
Shaft Diameter	6.35mm
Mounting Type	Panel Mount
Mounting Hole Diameter	15mm
Mechanical Rotation	285°
Rotational Life	100,000 cycles

## **Operation Environment Specifications**

Operating Temperature	-40°C to 105°C
Temperature Coefficient	±150 ppm/°C

## **Approvals**

Compliance/Certifications	2011/65/EU and 2015/863



