


## LP5K12103BW3

TeSys K reversing contactor - 3P(3 NO) - AC-3 - <= 440 V 12 A - 24 V DC coil



### Main

Range	TeSys
Product name	TeSys K
Product or component type	Reversing contactor
Device short name	LP5K
Contactor application	Motor control Resistive load
Utilisation category	AC-1 AC-3 AC-4
Device presentation	Preassembled with reversing power busbar
Poles description	3P
Pole contact composition	3 NO
[Ue] rated operational voltage	690 V AC 50/60 Hz for power circuit <= 690 V AC 50/60 Hz for signalling circuit
[Ie] rated operational current	20 A (<= 50 °C) at <= 440 V AC AC-1 for power circuit 16 A (<= 70 °C) at 690 V AC AC-1 for power circuit 12 A at <= 440 V AC AC-3 for power circuit
Motor power kW	3 kW at 220...230 V AC 50/60 Hz 4 kW at 480 V AC 50/60 Hz 4 kW at 500...600 V AC 50/60 Hz 4 kW at 660...690 V AC 50/60 Hz 5.5 kW at 380...415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz
Control circuit type	DC low consumption
Control circuit voltage	24 V DC
Auxiliary contact composition	1 NO
[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	20 A at <= 50 °C for power circuit 10 A at <= 50 °C for signalling circuit
Irms rated making capacity	110 A AC for signalling circuit conforming to IEC 60947 144 A AC for power circuit conforming to NF C 63-110 144 A AC for power circuit conforming to IEC 60947
Rated breaking capacity	110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947
[Icw] rated short-time withstand current	80 A 1 s signalling circuit 90 A 500 ms signalling circuit 110 A 100 ms signalling circuit 115 A <= 50 °C 1 s power circuit 105 A <= 50 °C 5 s power circuit 100 A <= 50 °C 10 s power circuit 75 A <= 50 °C 30 s power circuit 55 A <= 50 °C 1 min power circuit 50 A <= 50 °C 3 min power circuit 25 A <= 50 °C >= 15 s power circuit
Associated fuse rating	25 A gG at <= 440 V for power circuit 25 A aM for power circuit 10 A gG for signalling circuit conforming to IEC 60947 10 A gG for signalling circuit conforming to VDE 0660

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Average impedance	3 mOhm at 50 Hz - Ith 20 A for power circuit
[Ui] rated insulation voltage	690 V for power circuit conforming to IEC 60947-4-1 600 V for power circuit conforming to UL 508 690 V for signalling circuit conforming to IEC 60947-4-1 690 V for signalling circuit conforming to IEC 60947-5-1 600 V for signalling circuit conforming to UL 508 600 V for power circuit conforming to CSA C22.2 No 14 600 V for signalling circuit conforming to CSA C22.2 No 14
Electrical durability	0.3 Mcycles 20 A AC-1 at $U_e \leq 440$ V 1.3 Mcycles 12 A AC-3 at $U_e \leq 440$ V
Interlocking type	Mechanical
Mounting support	Plate Rail
Standards	BS 5424 IEC 60947 NF C 63-110 VDE 0660
Product certifications	CSA UL
Connections - terminals	Spring terminals 1 cable(s) 0.75...1.5 mm <sup>2</sup> - cable stiffness: solid Spring terminals 1 cable(s) 0.75...1.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end
Operating time	10...20 ms coil de-energisation and NO opening 30...40 ms coil energisation and NO closing
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical durability	5 Mcycles
Operating rate	3600 cyc/h

## Complementary

Coil technology	Built-in bidirectional peak limiting diode suppressor
Control circuit voltage limits	0.7...1.30 $U_c$ at $\leq 50$ °C operational 0.1...0.7 $U_c$ at $\leq 50$ °C drop-out
Inrush power in W	1.8 W at 20 °C
Hold-in power consumption in W	1.8 W at 20 °C
Heat dissipation	1.8 W
Auxiliary contacts type	Type instantaneous 1 NO
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Non overlap distance	0.5 mm
Insulation resistance	> 10 MOhm for signalling circuit

## Environment

IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-50...80 °C
Operating altitude	2000 m without derating in temperature
Flame retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
Mechanical robustness	Shocks contactor closed, on Z axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Z axis 10 Gn for 11 ms IEC 60068-2-27 Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor opened 2 Gn, 5...300 Hz IEC 60068-2-6

Shocks contactor opened, on X axis 10 Gn for 11 ms IEC 60068-2-27  
Shocks contactor opened, on Y axis 6 Gn for 11 ms IEC 60068-2-27  
Shocks contactor closed, on X axis 15 Gn for 11 ms IEC 60068-2-27  
Shocks contactor closed, on Y axis 10 Gn for 11 ms IEC 60068-2-27

Height	58 mm
Width	90 mm
Depth	57 mm
Product weight	0.49 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0825 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations