

1.07/3

Universal puller

3-arm pattern

Code	ETIM
1541757	ECOO2110
EAN	UNSPSC
4036976111408	27-11-17-12
Country of origin	eCl@ss
Germany	21-04-15-01
Customs tariff number	
82055980	



Article description

- Even load distribution over 3 legs ensures secure grip and balanced pull
- Strong, ergonomically shaped cross beam
- Hook red-hot drop-forged
- Pulling hook with proven screw connection for a frictional connection
- Can be used as external and internal puller by repositioning the legs
- Nitrocarburized spindle surface, wear and corrosion resistant
- Spindle remains smooth and clean - no need to grease or oil
- Crosspiece can be combined with other spindle/hook designs and lengths from the GEDORE puller construction kit
- Interchangeable legs available for several clamping depths

Article information

Contents (Qty of pieces)	1	Usable clamping reach [mm]	200 mm
Graduation	no	Clamping width (max.) external pulling [mm]	250 mm
reversible arms available	no	Spindle thread size	G 3/4 x 280
Clamping bracket available	no	Clamping width d_2 (min.) internal pulling [mm]	100 mm
Net weight [kg]	9,3 kg	Clamping width d_2 (max.) internal pulling [mm]	400 mm
Hook brake available	no	Width of hooked foot [mm]	36 mm
Hook can be moved parallel	no	Usable depth of hooked foot d_2 [mm]	28 mm
Quick release lever available	no	Thickness of hooked foot at tip	6,5 mm
3D data available	no	Width across flats [mm]	27 mm
Spindle anti-slip device	no	Tractive force (max.) [t]	7,5
Screws included	no	Hydraulic spindle optional	1.06/HSP2
Anti-slip device on the spindle	no	Number of arms	3
Can be retrofitted with hydraulic spindle	yes		