

The trusted value of OSRAM Digital Systems continues with Inventronics Global – where experience meets innovation.

BA-CX-L-HO-SQ -865-G6

BackLED CX L HO SQ G6



Product family features

- Each LED module contains 4 LEDs
- Compatible with Inventronics OPTOTRONIC constant voltage drivers / dimmers
- Color consistency in 3 SDCM
- Wide CCT and color options available
- IP66 rating
- Average lifetime (L70 B50): 50,000 h (temperature at $T_p = 50$ °C)

Product family benefits

- High module flux output up to 174 lm
- Lifetime (L70/B50): 50,000 h (temperature at $T_c = 75$ °C)
- Switch times up to 1,000,000 h
- Wide beam angle for high uniformity
- Good solution to reduce system cost
- Backside injection technology for high protection level



Specifications are subject to changes without notice.

www.inventronicsglobal.com

© 2024, Inventronics GmbH. All rights reserved.

support@inventronicsglobal.com

Areas of application

- Channel letters
- Signage boxes
- Sky Ceiling
- Petrol station, Gas station
- Luminous areas and ceilings
- Backlighting

Technical data

Electrical data

Nominal voltage	12.0 V
Rated wattage	30.00 W
Input voltage range	12...13 V
Accidental reverse input voltage protection up to	13 V
Nominal wattage per chain	30.00 W
Nominal wattage per LED module	1.5 W

Photometrical data

Color rendering index Ra	80
Luminous efficacy	116 lm/W
Light color (designation)	Cool White
Color Temperature	6500
Luminous flux per LED module	174 lm


Light technical data

Beam angle	155 °
------------	-------

LED module information

Number of LEDs per module	4
Number of LED modules per chain	20

Dimensions & weight



Length	4200 mm
Width	31.3 mm
Height	10.2 mm
Product weight	170.00 g
Module pitch	200 mm
Module length	36.6 mm

Temperatures & operating conditions

Ambient temperature range	-30...+50 °C
----------------------------------	--------------

Lifespan

Rated lamp life time	50000 h
----------------------	---------

Capabilities

Dimming range	1...100 %
---------------	-----------

Certificates & standards

Approval marks – approval	CE / BIS / CB
Energy efficiency class of the contained light source	F

Logistical data

Commodity code	8539510000
----------------	------------

Environmental information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Date of Declaration	26-09-2025
Primary Article Identifier	6937186107558 6937186160881
Candidate List Substance 1	no declarable substance contained
CAS No. of substance 1	no declarable substance contained
Declaration No. in SCIP database	In work
SCIP_ID	

Ecodesign regulation information:

- This product is considered to be a "containing product" in the sense of Regulations (EU) 2019/2020 and (EU) 2019/2015.
- Tolerances of the reported values, are according to LED Modules Performance standard IEC/EN 62717.
- In general, the replacement of the contained light sources without permanent damage to the product with the use of common available tools is possible in the final application when they can be dismantled from the installation environment and substituted for the necessary number of light sources restoring its full electrical/mechanical/thermal/optical functionality by means of a professional installer.
- Dismantling of light sources from containing products at end of life: Containing products with light sources which are scalable in length can be cut to the length of the contained light source and if applicable mechanically detached from protective and/or optical covers. Containing products shall be separated from building material and/or from other additional mounting accessories by means of a professional installer. Separate control gear and light sources must be disposed of at certified disposal companies in accordance with Directive 2012/19/EU (WEEE) in the EU and with Waste Electrical and Electronic Equipment (WEEE) Regulations 2013 in the UK. For this purpose, collection points for recycling centres and take-back systems (CRSO) are available from retailers or private disposal companies, which accept separate control gear and light sources free of charge. In this way, raw materials are conserved and materials are recycled.

Additional product information

- Installation of LED modules (with power supplies) needs to be made under consideration of all valid regulations and norms.
- Installation by qualified electrician only.
- Please see the relevant application guides and instructions sheets for more detailed safety and mounting information. Additional information is available on request.
- The LED module itself and all its components must not be stressed mechanically.
- To avoid mechanical damage, the LED modules have to be attached securely to the intended mounting surface. It is recommended to avoid heavy vibration.
- Only a qualified electrician may install the module.
- Observe correct polarity and wiring diagrams! Incorrect polarity or wrong wiring can cause unpredictable permanent damage or even failure of the product.
- Assembly must not damage or destroy conducting paths on the circuit board.
- Please ensure that the power supply is of adequate power to operate the total load.
- LED modules are dimmable by means of PWM (pulse width modulation). It is recommended using SELV CV drivers from Inventronics.
- Pay attention to standard ESD precautions when installing the module.
- Damage caused by corrosion will not be accepted as a material defect claim. It is the manufacturer's responsibility to provide suitable protection against corrosive agents, such as moisture, condensation and other harmful elements.
- For applications involving exposure to humidity and dust the module must be protected by a fixture or housing with a suitable IP protection class.

Download Data

File		
IES data	Compressed	▶ BA-CX-L-Ho-SQ-865-G6.1
Product Datasheet	PDF	▶ Product Datasheet_BackLED® Core Xperience G6
Certificates	PDF	▶ CB NL-113263-151239
Eulumdat	Compressed	▶ BA-CX-L-HO-SQ-865-G6.1_LTD file
CAD data 3-dim	Compressed	▶ CX-4LED-3D-BA-CX-G6
Mandatory Publications	PDF	▶ CED 9C1-4539768-EN-00_24-12
User instruction	PDF	▶ 15130306 UI_BA-CX-G6_8s_MiC_INV

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
6937186107558 OSRAM	BA-CX-L-HO-SQ -865- G6	Shipping carton box 25 Pieces	360 x 260 x 240 mm	22.46 dm ³	195.00 g
6937186160881 INVENTRONICS	BA-CX-L-HO-SQ -865- G6	Shipping carton box 25 Pieces	360 x 260 x 240 mm	22.46 dm ³	280.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit