

Description

CHROME SWIVEL TOP PLATE CASTOR, GREY RUBBER 80mm, 70kg

Part Number

Swivel
165301400A

Swivel with brake
165301420A



	Swivel	Swivel + Brake
Wheel Diameter ØD	80 mm	
Overall Height H	113 mm	
Size of plate	93x64 mm	
Plate hole centers	75x45 mm	
Plate hole	8,5 mm	
Spacing between castor flanges	35 mm	
Offset F ±1	30 mm	30 mm
Axle Type	Bolt M8	
type de moyeu	2 Ball bearings	
Hub Length	33 mm	
Wheel Bore Diameter	8 mm	
Tread Width	25 mm	
Tread Width on the ground	21 mm	
Hardness Tread shore A ± 5	80	
Load capacity	70 Kg	
Weigth	0,57 kg	0,66 kg

Castor Assembly :

Chrome-plated pressed steel, swivel on two rows of balls
Upper row protected by plastic seal. Sheet metal thickness 2mm
Total lock (wheel and swivel). Short steel brake pedal.
Fastening by top plate

Wheel :

Wheel center made of grey polypropylene RAL 7037
Tread : Thermoplastic rubber, grey non marking. Two ball bearings.
Chrome-plated steel threadguards.

Features :

Silent and easy to push and pull which reduces the risk of injury and disorders to the individual using the product
Attractively designed, shiny chrome.
Easily accessible steel brake pedal
Non-marking thermoplastic rubber tyre fitted
Robust.