

TeSys LE - enclosure for DOL starter - without pushbuttons

Local distributor code:

402711599 DE1DS1A04

EAN Code: 3389110087062

Main

Range of product	TeSys
Range	TeSys
Device short name	DE1D
Product or component type	Enclosure
Material	Polycarbonate
Device composition	Contactor ordered separately Thermal overload relay ordered separately
Product compatibility	LE1D12 LE1D09
Control type	Without

Complementary

Cable entry number	2 ISO20 top 2 ISO20 bottom 2 Pg 13 bottom 2 Pg 16 bottom
Height	166 mm
Width	88 mm
Depth	135 mm
Net weight	0.3 kg

Environment

IP degree of protection	IP65 conforming to IEC 60529	
IK degree of protection	IK07 conforming to IEC 60529	
Ambient air temperature for operation	-540 °C	
Environmental characteristic	Standard environment	
Product certifications	UKCA	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.500 cm
Package 1 Width	20.000 cm
Package 1 Length	23.000 cm

Package 1 Weight	486.000 g
Unit Type of Package 2	P06
Number of Units in Package 2	30
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	27.730 kg

Logistical informations

Country of origin FR

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	107
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No