

ENGLISH

Datasheet

RS Pro Recessed Indicator Panel Mount, 8mm Mounting Hole Size, Blue LED, Lead Pins Termination, 5 mm Lamp Size, 2 V dc

RS Stock No: 212-109



Product Details

RS Pro prominent indicator with 8 mm mounting hole, features blue LEDs for panel mount applications. With an IP67 rating, it is suitable for most environments including outdoor applications. This indicator accommodates a lamp size of 5 mm and offers short body pin termination. It has a voltage rating of 3.3 V. The indicator has a wide operating temperature range of -40 to +85°C, further increasing the potential applications they may be used for. The 5 mm LED requires an 8 mm panel cut-out and is supplied with a fixing nut and spring washer. It offers a wide selection of voltage ratings, bezel finishes and bezel styles.

Features and Benefits

- 8 mm panel mounting LED indicator
- Coloured diffused epoxy lens or water clear super bright LEDs
- · Prominent, recessed, chamfer and flush bezel styles
- Sealed to IP67
- Operating temperature range: -40 to +85°C






Specifications:

Bezel Colour	Bright Chrome	
Bezel Style	Prominent	
Current Rating	20 mA	
Intensity	1600 mcd	
IP Rating	IP67	
Lamp Size	5 mm	
Lamp Type	LED	
Length	17.6 mm	
Light Output Colour	Blue	
Mounting Hole Size	8 mm	
Termination Type	Short Body Pins	
Type	Panel Mount	
Voltage Rating	3.3 V	
Temperature Rating	-40 to +85°C	
LED Colour	Blue	
Type of Illumination	Fixed Light	



TECHNICAL SPECIFICATIONS					
Voltage	Operating Voltage	Operating Current			
-	(Min to Max)	(Typical All Types)			
02 (No Resistor)	1.8 to 3.3VDC	20mA max*			
6VDC	5.4 to 6.6VDC	20mA			
12VDC	10.8 to 13.2VDC	20mA			
24VDC	21.6 to 26.4VDC	20mA			
28VDC	25.2 to 30.8VDC	20mA			
110VAC	99 to 121VAC	6mA			
220VAC	207 to 253VAC	3mA			

ENGLISH



Standard LED Intensity	Prominent and Recessed	Flush	Forward Voltage		
HE Red	80mcd	8mcd	2.0V		
Green	60mcd	6mcd	2.2V		
Yellow	50mcd	6mcd	2.1V		
Blue	1600mcd	50mcd	3.3V		
White	1600mcd	500mcd	3.3V		
Orange	60mcd	110mcd	2.2V		
Bi-color (Typical) (Red/Green)	14/30mcd	15/10mcd	2.0V/2.2V		
Tri-color (Typical) (Red/Green/Yellow)	60/15/13mcd	15/10/6mcd	2.0V/2.2V/2.1V		
Bi-color - The color is changed by reversing the polarity of the supply voltage.					
Tri-color - The indicator has red and green LEDs, when both connected yellow is produced.					
Super Bright LED	Prominent and Recessed	Flush	Forward Voltage		
HE Red	5,000mcd	1,300mcd	2.2V		
Green	10,000mcd	1,200mcd	3.3V		
Yellow	4,000mcd	350mcd	2.0V		
Blue	2,200mcd	280mcd	3.3V		
White	2,500mcd	950mcd	3.3V		
Orange	4,000mcd	500mcd	2.2V		
Hyper Bright LED	Prominent and Recessed	Flush	Forward Voltage		
HE Red	6,000mcd	980mcd	2.2V		
Green	1,900mcd	300mcd	3.3V		
Yellow	1,600mcd	250mcd	2.0V		
Orange	2,400mcd	110mcd	2.2V		
Luminous intensity will be reduced with lower operating current.					

Note: The operating voltage must not be exceeded by more that 10% as this will result in reduced life expectancy. The company reserves the right to change specifications without notice.

* Customer to supply resistor for desired operating current. Luminous intensity is measured at 20mA on a discrete LED unless otherwise stated. Luminous intensities and color shades of white LEDs may vary within a batch. LED characteristics are dependent upon environmental conditions. Therefore published data should be considered nominal.



ENGLISH

Technical Drawings

PROMINENT BEZEL

