



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: UV-329 (1% in 16524382162) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 2359482-1
LUMAWISE ENDURANCE N+ 7P Base
With Vent



TE Part # 2359482-5
LUMAWISE ENDURANCE N+ 3P Base
With Vent



TE Part # 2359482-4
LUMAWISE ENDURANCE N+ 5P Base



TE Part # 2359482-2
LUMAWISE ENDURANCE N+ 7P Base




TE Part # 2359482-3
LUMAWISE ENDURANCE N+ 5P Base
With Vent



TE Part # 2359482-6
LUMAWISE ENDURANCE N+ 3P Base

Customers Also Bought



TE Part #826926-5
5P AMPMODU II STIFT LEI



TE Part #1-1123722-7
3.96 EP PLUG HSG 7P(NATURAL)




TE Part #6-1393243-8
RT424024



TE Part #2-1437565-7
FSM2JSMA=SMT,TACTILE,PB SWITCH



TE Part #6-1625892-1
3W SM M/OX 5% 5K6



TE Part #1776275-2
2P TB ,90deg,VT,3.5mm,Blue,w
/interlock



TE Part #2328823-1
LUMAWISE S 80MM DIA DOME
SMOKE GRAY LOW



TE Part #1-2343404-1
MODULE ASSY,80MM LUMAWISE S,
KEYED,vented



TE Part #2359482-1
LUMAWISE ENDURANCE N+ 7P Base
With Vent



TE Part #1-2363638-2
Rcpt,LUMAWISE Endurance S2 Kit,
KeyA,Dots



Documents

Product Drawings

LUMAWISE ENDURANCE N+ Gray Short Dome

English

CAD Files

Customer View Model

ENG_CVM_CVM_2359615-1_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2359615-1_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2359615-1_A1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

LUMAWISE ENDURANCE N+ Network Lighting Controls

English

Product Specifications

Application Specification

English

Agency Approvals

UL_CERT_CB_4789600659_TR_C1

English

UL_CERT_CB_US_37285_C1

English