



ENGLISH

Datasheet

Stock No: 811-4352

# RS Pro BASEC 3 Core Grey Unscreened 2183Y Solid PVC Power Cable H03VV-F, 0.75 mm<sup>2</sup> CSA 6 A, 300 V



NEW  
LOWER  
PRICE

Image representative of range

## Product Details

### BASEC approved H03VV-F/2183Y 3 Core Cable

2183Y 3 core cable can be used with household applications in covered, dry, steamed and humid areas where low mechanical stress exists

### Features and Benefits

- Flexible, 3 core cable with fine stranded copper conductors
- PVC sheath
- PVC insulation

## Standards

BASEC

Flexible PVC Cable

## Specifications:

Number of Cores	3
Cross Sectional Area	0.75 mm <sup>2</sup>
Sheath Colour	Grey
Current Rating	6 A
Voltage Rating	300 V
Outer Diameter	6.7mm
Sheath Material	Polyvinyl Chloride PVC
Harmonised Code	H03VV-F
Type	2183Y
Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+70°C
Screened/Unscreened	Unscreened
Conductor Strand Type	Solid
Insulation Material	PVC
Number of Strands	24
Size of Strands	0.2 mm
American Wire Gauge	18 AWG
Core Strands	24/0.2 mm
Conductor Resistance	26 Ω/km
Standards Met	BASEC
Conductor Material	Copper