

# LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3  
OF MANUAL OF TESTS AND CRITERIA



N/A = Not Applicable

## 1. Name of cell / battery

2347-3008-01 Li-Ion Battery 3,7V 2600mAh with Safetyboard

## 2. Manufacturer of cell / battery / product

Name	Ansmann AG
Address	Industriestr. 10, 97959 Assamstadt
Phone	+49 6294 4204-0
Email	info@ansmann.de
Website	www.ansmann.de

## 3. Test laboratory of cell / battery / product

Name	Ansmann AG Testzentrum
Address	Industriestr. 10, 97959 Assamstadt
Phone	+49 6294 4204-0
Email	info@ansmann.de
Website	www.ansmann.de

## 4. ID-number and date

Unique test report identification number	TZ_000061_UN	Date of test report	14.11.2014
--	--------------	---------------------	------------

## DESCRIPTION OF CELL / BATTERY

### 5. Mark the type of cell/battery with an "•"

<input type="radio"/> Lithium ion cell	<input type="radio"/> Lithium metal cell
<input checked="" type="radio"/> Lithium ion battery	<input type="radio"/> Lithium metal battery

## 6. Parameters

	Cell	Battery
Mass in gram (g):		49
Lithium ion: Indicate watt-hour rating (Wh):		9,62
Lithium metal: Indicate lithium metal content in gram (g):		2,4

## 7. Physical description of cell / battery

Li-Ion

# LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3  
OF MANUAL OF TESTS AND CRITERIA



<b>Name of cell/battery</b> (taken from field 1)
2347-3008-01 Li-Ion Battery 3,7V 2600mAh with Safetyboard

<b>8. Model numbers</b>
2347-3008-01; 2347-3008-02; 2347-3008-03; 2347-3008-04; 2347-3008-05

## TESTS AND RESULTS

9. List of tests conducted and results - Mark N/A, pass or fail with an "•"	N/A	pass	fail
T1 - Altitude simulation	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T2 - Thermal Test	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T3 - Vibration	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T4 - Shock	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T5 - External Short Circuit	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T6 - Impact / Crush	<input checked="" type="radio"/>	<input type="radio"/>	<input type="radio"/>
T7 - Overcharge	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T8 - Forced Discharge	<input checked="" type="radio"/>	<input type="radio"/>	<input type="radio"/>
T6 - Impact Cell	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T6 - Impact Cell	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>

<b>10. Reference to assembled battery testing requirements</b>		
Information UN-Test Cell: UN Test Manual of Test and Criteria ST/SG/AC.10/11/Rev.5 ID-number and date QAE-EF02-100531-CY018650B4 2010.05.31	N/A	<input type="text"/>

<b>11. Reference to the revised edition of the Manual of Tests and Criteria used and to amendments thereto</b>
ST-SG-AC10-11-Rev5-Amend.1-38.3

<b>12. The manufacture of the cell / battery is in accordance with the documented quality management system as required by the regulations.</b>
---

<b>13. Place, Date</b>	<b>14. Title, Surname, First name</b>	<b>15. Company stamp and signature</b>
Assamstadt	Adrian Selke	Selke, Adrian <small>Digital unterschrieben von Selke, Adrian Datum: 2019.12.02 10:28:24 +01'00'</small>