



DCD785L2

18V XR Li-Ion Compact Hammer Drill/Driver

- Latest generation 18V XR Li-Ion compact hammer drill/driver featuring NEW XR Li-Ion battery technology
- Ultra compact, lightweight design allows use in confined spaces
- Two speed all metal transmission for increased runtime and longer tool life

FEATURES

Latest generation 18V XR Li-Ion compact hammer drill/driver featuring NEW XR Li-Ion battery technology
Ultra compact, lightweight design allows use in confined spaces
Two speed all metal transmission for increased runtime and longer tool life
14 position adjustable torque control for consistent screwdriving into a variety of materials with different screw sizes
Intelligent trigger design allows for total control of application.
Compact 13mm single sleeve keyless chuck with automatic spindle lock for quick and easy bit change with one hand
Bright white LED with delay feature for improved visibility and flashlight functionality.
Improved ergonomic design and rubber grip improves user comfort
Li-Ion slide pack battery allows for superior insertion and removal
Multi voltage charger for use with 18V, 14.4V and 10.8V XR Li-Ion slide pack batteries
Steel belt clip and tough magnetic bit holder ensures strong storage solutions
Part of the intelligent XR Lithium Ion Series designed for efficiency and making applications faster.

STANDARD

55 minute charger
2 x Slide pack batteries
Heavy duty carry case

SPECIFICATIONS

Voltage	18 V
Battery Capacity	3.0 Ah
Chuck Capacity	1.5 - 13 mm
Power Output	350 Watts
No Load Speed	0-600/2,000 rpm
Beats per Minute	0-10,200/34,000 bpm
Max Torque	60 Nm
Max. Drilling Capacity [Wood]	38 mm
Max. Drilling Capacity [Metal]	13 mm
Max. Drilling Capacity [Masonry]	13 mm
Weight	1.88 kg
Length	202 mm
Height	236 mm
Spindle Thread	
Width	80 mm
Voltage	