



Fiber Optics > Fiber Optic Connectors > Rugged Fiber Connectors > Expanded Beam Fiber Optics



Fiber Optic Product Type: **Cable Adapter Kit**

Bulkhead Style: **Standard**

Shell Material: **Aluminum Alloy**

Features

Product Type Features

Fiber Optic Product Type	Cable Adapter Kit
--------------------------	-------------------

Body Features

Shell Finish	Hard Anodize
Bulkhead Style	Standard

Housing Features

Shell Material	Aluminum Alloy
----------------	----------------

Dimensions

Compatible Cable Diameter (Max)	5 mm
---------------------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (3% in 74018813) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1918943-1  
SHELL KIT, STD SQ FLG PRO BEAM JR HA




TE Part # 1918939-1  
SHELL KIT, STD BULKHEAD, PRO BEAM JR, HA


Customers Also Bought




TE Part #NB19234001  
RNF-100-1/8-CL-SP




TE Part #1445692-1  
ASY,PIN,QUADRAX




TE Part #1588908-1  
PRO BEAM JR, FRRL KIT, PC 126 SEALED




TE Part #1445693-1  
SOCKET CONTACT,QUADRAX,SZ8,RR




TE Part #YMC8016-F-13-04SNO  
ARINC 801, 38999 STYLE, SIZE 13-04



TE Part #ZPF000000000100854  
DMC-MD 20 B



TE Part #1-640721-0  
06P UMNL STR/REL & INSRT NATL



TE Part #1515739-1  
INSERT ASSY, 2 X 1310/1550 SM, JR



Documents

Product Drawings

STD CABLE ADAPTER, No Boot, HA, 5.0 mm

English

CAD Files

Customer View Model

ENG\_CVM\_1918934-3\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_1918934-3\_A.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_1918934-3\_A.2d\_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Rugged Fiber Optics

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English