

STRADA-2X2-MEW

Beam with extremely low glare fulfilling EN13201 M-class requirements for wet road surfaces in North Europe


TECHNICAL SPECIFICATIONS:

Dimensions	50.0 mm
Height	10.2 mm
Fastening	screw
Colour	clear
Box size	480 x 280 x 300 mm
Box weight	9.6 kg
Quantity in Box	800 pcs
ROHS compliant	yes ⓘ



MATERIAL SPECIFICATIONS:



Component	Type	Material	Colour
STRADA-2X2-MEW	Multi-lens	PMMA	clear




PHOTOMETRIC DATA (MEASURED):




LED XD16
 FWHM Asymmetric
 Efficiency 94 %
 Peak intensity 0.700 cd/lm
 LEDs/each optic 4
 Light colour White
 Required components:




LED XD16
 FWHM Asymmetric
 Efficiency 94 %
 Peak intensity 1.100 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED XP-G2
 FWHM Asymmetric
 Efficiency 94 %
 Peak intensity 1.100 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LED XP-G3
 FWHM Asymmetric
 Efficiency 86 %
 Peak intensity 0.800 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




PHOTOMETRIC DATA (MEASURED):




LED XP-L HI
 FWHM Asymmetric
 Efficiency 94 %
 Peak intensity 1.100 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





LED LUXEON 5050
 FWHM Asymmetric
 Efficiency 94 %
 Peak intensity 0.720 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:






LED LUXEON TX
 FWHM Asymmetric
 Efficiency 92 %
 Peak intensity 1.100 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED LUXEON V
 FWHM Asymmetric
 Efficiency 94 %
 Peak intensity 0.770 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):


<p>NICHIA</p> <p>LED NVSW219D FWHM Asymmetric Efficiency 94 % Peak intensity 0.990 cd/lm LEDs/each optic 1 Light colour White Required components:</p>	
<p>NICHIA</p> <p>LED NVSW319B FWHM Asymmetric Efficiency 94 % Peak intensity 0.800 cd/lm LEDs/each optic 1 Light colour White Required components:</p>	
<p>OSRAM</p> <p>LED PrevaLED Brick HP 2x8 FWHM Asymmetric Efficiency 87 % Peak intensity 0.950 cd/lm LEDs/each optic 1 Light colour White Required components:</p>	
<p>OSRAM <small>Opto Semiconductors</small></p> <p>LED OSLOM Square CSSRM2/CSSRM3 FWHM Asymmetric Efficiency 87 % Peak intensity 0.950 cd/lm LEDs/each optic 1 Light colour White Required components: Undefined Manufacturer: Protective Plate, Glass</p>	

PHOTOMETRIC DATA (MEASURED):

OSRAM


Opto Semiconductors

LED OSLON Square PC
 FWHM Asymmetric
 Efficiency 94 %
 Peak intensity 1.100 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




PHILIPS

LED Fortimo FastFlex LED 2x8 DA G4
 FWHM Asymmetric
 Efficiency 94 %
 Peak intensity 1.100 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




SAMSUNG

LED HiLOM RH16 (LH351C)
 FWHM Asymmetric
 Efficiency 94 %
 Peak intensity 0.990 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





SEOUL SEMICONDUCTOR

LED Z5M3
 FWHM Asymmetric
 Efficiency 94 %
 Peak intensity 0.890 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):

			
SEoul SEMICONDUCTOR			
LED	Z8Y22		
FWHM	Asymmetric		
Efficiency	94 %		
Peak intensity	0.890 cd/lm		
LEDs/each optic	1		
Light colour	White		
Required components:			




TRIDONIC

LED	RLE 2x4 2000lm HP EXC2 OTD
FWHM	Asymmetric
Efficiency	94 %
Peak intensity	1.200 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	

TRIDONIC

LED	RLE 2x8 4000lm HP EXC2 OTD
FWHM	Asymmetric
Efficiency	94 %
Peak intensity	1.200 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



PHOTOMETRIC DATA (SIMULATED):

CREE

LED XHP35 HD
FWHM Asymmetric
Efficiency %
Peak intensity cd/lm
LEDs/each optic 1
Light colour White
Required components:

CREE


LED XHP35 HI
FWHM Asymmetric
Efficiency %
Peak intensity cd/lm
LEDs/each optic 1
Light colour White
Required components:

CREE

LED XM-L2
FWHM Asymmetric
Efficiency 0 %
Peak intensity 0.000 cd/lm
LEDs/each optic 1
Light colour White
Required components:

CREE

LED XP-L HD
FWHM Asymmetric
Efficiency 93 %
Peak intensity 0.850 cd/lm
LEDs/each optic 1
Light colour White
Required components:




PHOTOMETRIC DATA (SIMULATED):



LED XP-L HI
FWHM Asymmetric
Efficiency %
Peak intensity cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED XP-L2
FWHM Asymmetric
Efficiency 94 %
Peak intensity 0.800 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED XT-E
FWHM Asymmetric
Efficiency %
Peak intensity cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED NCSxx19B
FWHM Asymmetric
Efficiency 0 %
Peak intensity 0.000 cd/lm
LEDs/each optic 1
Light colour White
Required components:

PHOTOMETRIC DATA (SIMULATED):


<p>NICHIA</p> <p>LED NVSxE21A FWHM Asymmetric Efficiency 94 % Peak intensity 1.100 cd/lm LEDs/each optic 1 Light colour White Required components:</p>	
<p>NICHIA</p> <p>LED NVSxE21A FWHM Asymmetric Efficiency 86 % Peak intensity 0.960 cd/lm LEDs/each optic 1 Light colour White Required components: Undefined Manufacturer: Protective Plate, Glass</p>	
<p>NICHIA</p> <p>LED NVSxx19B/NVSxx19C FWHM Asymmetric Efficiency 0 % Peak intensity 0.000 cd/lm LEDs/each optic 1 Light colour White Required components:</p>	
<p>OSRAM Opto Semiconductors</p> <p>LED Duris S8 FWHM Asymmetric Efficiency % Peak intensity cd/lm LEDs/each optic 1 Light colour White Required components:</p>	

PHOTOMETRIC DATA (SIMULATED):

OSRAM


Opto Semiconductors

LED OSCONIQ P 3737 (2W version)
FWHM Asymmetric
Efficiency 94 %
Peak intensity 1.000 cd/lm
LEDs/each optic 1
Light colour White
Required components:




PHILIPS

LED Fortimo FastFlex LED 2x8 DAX G4
FWHM Asymmetric
Efficiency 94 %
Peak intensity 0.880 cd/lm
LEDs/each optic 1
Light colour White
Required components:



SAMSUNG

LED LH351D
FWHM Asymmetric
Efficiency 94 %
Peak intensity 0.800 cd/lm
LEDs/each optic 1
Light colour White
Required components:



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)